

TS15X5 ST MPC1217 VER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

Accessories

General ordering data

Version	Rail, TS 15, Width: 4.13 mm, without slot, Steel, galvanized, chromium-plated
Order No.	8000037598
Type	TS15X5 ST MPC1217 VER
GTIN (EAN)	4050118653106
Qty.	20 items

TS15X5 ST MPC1217 VER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5.5 mm	Depth (inches)	0.2165 inch
Height	0.59 mm	Height (inches)	0.0232 inch
Width	4.13 mm	Width (inches)	0.1626 inch
Net weight	18.28 g		

Temperatures

Operating temperature	
-----------------------	--

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Material thickness	1 mm	Installation advice	Direct mounting
Standards	DIN EN 60715	Surface finish	galvanized, chromium-plated
Basic material	Steel	Integral fixing	Screwed

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		