


POK COPL 081106 MSZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Version	Klippon POK (polyester empty enclosure), Earthing plate, with functional earth connection, Height: 36.87 mm, Width: 129.61 mm, Depth: 0.75 mm, Basic material: Steel sheet zinc plated
Order No.	8000191930
Type	POK COPL 081106 MSZN
GTIN (EAN)	4069165099423
Qty.	5 items

Technical data**Dimensions and weights**

Depth	0.75 mm	Depth (inches)	0.0295 inch
Height	36.87 mm	Height (inches)	1.4516 inch
Width	129.61 mm	Width (inches)	5.1027 inch
Net weight	23.4 g		

Temperatures

Operating temperature

General information

Material thickness	0.75 mm	Basic material	Steel sheet zinc plated
--------------------	---------	----------------	-------------------------

Classifications

ETIM 8.0	EC002623	ETIM 9.0	EC002623
ETIM 10.0	EC002623	ECLASS 14.0	27-18-28-14
ECLASS 15.0	27-18-28-14		