



SRC 2CO N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	RIDERSERIES RCL, Relay socket, Number of contacts: 2, CO contact, Screw connection
Order No.	8693930000
Type	SRC 2CO N
GTIN (EAN)	4032248365418
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-03-31T00:00:00+02:00
Alternative product	CSL S 2CO

SRC 2CO N

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E223759

Dimensions and weights

Depth	50 mm	Depth (inches)	1.9685 inch
Height	77 mm	Height (inches)	3.0315 inch
Width	15.5 mm	Width (inches)	0.6102 inch
Net weight	41 g		

Temperatures

Storage temperature	-40 °C...70 °C	Ambient temperature	-40 °C...70 °C
Operating temperature		Humidity	40 °C / 93 % rel. humidity, no condensation

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Rated data UL

Certificate No. (cURus)	E223759
-------------------------	---------

Load side

Contact type	2 CO contact
--------------	--------------

General data

Version	flat design	Mounting rail	TS 35
Colour	black		

Insulation coordination

Dielectric strength, Input/Output	2.5 kVeff / 1 Min.	Dielectric strength of neighbouring contacts	2.5 kVeff / 1 Min.
Protection degree	IP20		

Further details of approvals / standards

Standards	UL508	Certificate No. (cURus)	E223759
-----------	-------	-------------------------	---------

Connection data

Wire connection method	Screw connection	Tightening torque, min.	0.5 Nm
Tightening torque, max.	0.8 Nm	Blade size	size PH1
Pitch in mm (P)	5.00 mm		

Technical data

Classifications

ETIM 8.0	EC001456	ETIM 9.0	EC001456
ETIM 10.0	EC001456	ECLASS 14.0	27-37-16-03
ECLASS 15.0	27-37-16-03		