

MI8A-I/O S SUBD15B**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Specific adapter to be connected to the MICROSERIE RELAYS using a 10-pole flat-cable connector or 15-pole Sub-D connector.

General ordering data

Version	Adapter, MICRO-Interface, IEC 60603/DIN41612 plug-in connectors, Screw connection
Order No.	8800220000
Type	MI8A-I/O S SUBD15B
GTIN (EAN)	4032248497157
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Available until	2026-02-10T00:00:00+01:00

MI8A-I/O S SUBD15B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	61 mm	Depth (inches)	2.4016 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	32 mm	Width (inches)	1.2598 inch
Net weight	27.46 g		

Temperatures

Storage temperature	-20...85 °C	Operating temperature	0...50 °C
---------------------	-------------	-----------------------	-----------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6aI, 6c
REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3
SCIP	a009610c-b9bf-4453-8f5a-4b028e0ef0cc

Connection data

Supply voltage	max. 30 V AC/DC
----------------	-----------------

Ratings data

Operating voltage	30 V UC	Max. current per channel	0.5 A
Total operating current	2 A		

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 50 V AC
Surge voltage category	III	Pollution severity level	2
Insulation test voltage AC	0.35 kV		

Supply connection

Type of connection	Screw connection
--------------------	------------------

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		