

SCM-I CLIP N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Retaining clip for RIDERSERIES RCM relays

- Metal and plastic retaining clip

General ordering data

Version	RIDERSERIES RCM, Retaining clip
Order No.	8875620000
Type	SCM-I CLIP N
GTIN (EAN)	4032248608577
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Available until	2026-06-30T00:00:00+02:00
Alternative product	CXM CLIP P

SCM-I CLIP N

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	55.5 mm	Depth (inches)	2.185 inch
Height	24 mm	Height (inches)	0.9449 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	3.74 g		

Temperatures

Storage temperature	-40 °C...85 °C	Ambient temperature	-40 °C...70 °C
Operating temperature		Humidity	40 °C / 93 % rel. humidity, no condensation

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Version	for low screw connection base	Basic material	Plastic
Colour	orange		

Classifications

ETIM 8.0	EC002586	ETIM 9.0	EC002586
ETIM 10.0	EC002586	ECLASS 14.0	27-37-16-92
ECLASS 15.0	27-37-16-92		

Drawings

Dimensional drawing

