

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

Version	Crimping tool for wire-end ferrules, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Square crimp
Order No.	<a href="#">9017360000</a>
Type	PZ 3 ZERT
GTIN (EAN)	4008 190466688
Qty.	1 items

**PZ 3 ZERT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	410.08 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

**Technical data**

Description of article	(1)Crimping tool	Version	Mechanical, without interchangeable inserts
------------------------	------------------	---------	---

**Description of contact**

Type of contact	Wire-end ferrules with/without plastic collars	Conductor cross-section, max. AWG	AWG 10
Conductor cross-section, min. AWG	AWG 21	Crimping range, max.	6 mm <sup>2</sup>
Crimping range, min.	0.5 mm <sup>2</sup>		

**tool data crimping**

Drive	mechanical	Wire end ferrules cross-section, max.	6 mm <sup>2</sup>
Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>	Crimping type/profile	Square crimp

**Classifications**

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

**PZ 3 ZERT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## PZ 3 ZERT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Accessories / replacement parts



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

## General ordering data

Type	ERES PZ 3N	Version	
Order No.	<a href="#">1287130000</a>		
GTIN (EAN)	4050118077834		
Qty.	1 ST		

## Replacement parts



After stripping the insulation, a suitable contact or wire end ferrule can be crimped onto the end of the cable. Crimping forms a secure connection between conductor and contact and has largely replaced soldering. Crimping denotes the creation of a homogeneous, permanent connection between conductor and connecting element. The connection can be made only with high-quality precision tools. The result is a secure and reliable connection both in mechanical and electrical terms. Weidmüller offers a wide range of mechanical crimping tools. Integral ratchets with release mechanisms guarantee optimum crimping. Crimped connections made with Weidmüller tools comply with international standards and regulations.

## General ordering data

Type	ERTE GRIFFE PZ	Version	
Order No.	<a href="#">9202810000</a>	Pressing tool, Replacement part	
GTIN (EAN)	4032248512577		
Qty.	1 ST		

## in multipack bag



- In multi-pack bag
- Weidmüller colour code

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	H1,5/17,5X SW SV	Version
Order No.	<a href="#">9006590000</a>	Wire-end ferrule, Standard, 13 mm, 8 mm, black
GTIN (EAN)	4008190332259	
Qty.	100 ST	
Type	H1,5/19,5X SW SV	Version
Order No.	<a href="#">9006630000</a>	Wire-end ferrule, Standard, 15 mm, 10 mm, black
GTIN (EAN)	4008190332266	
Qty.	100 ST	

### supplied loose in polybag



- In multi-pack bag
- Weidmüller colour code

### General ordering data

Type	H1,5/24 XS SW	Version
Order No.	<a href="#">9202870000</a>	Wire-end ferrule, Standard, 18 mm, 14.5 mm, black
GTIN (EAN)	4032248517947	
Qty.	100 ST	

### in multipack bag



- supplied loose in polybag
- Weidmüller colour code

### General ordering data

Type	H2,5/17,5X BL SV	Version
Order No.	<a href="#">9006670000</a>	Wire-end ferrule, Standard, 14 mm, 8 mm, blue
GTIN (EAN)	4008190332273	
Qty.	100 ST	
Type	H2,5/21,5X BL SV	Version
Order No.	<a href="#">9006710000</a>	Wire-end ferrule, Standard, 17 mm, 12 mm, blue
GTIN (EAN)	4008190332280	
Qty.	100 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### supplied loose in polybag



- supplied loose in polybag
- Weidmüller colour code

### General ordering data

Type	H2,5/24 XS BL	Version	
Order No.	<a href="#">9202880000</a>	Wire-end ferrule, Standard, 18 mm, 14.5 mm, blue	
GTIN (EAN)	4032248517954		
Qty.	100 ST		

### in multipack bag



- Polypropylene conical cable entry
  - Heat-resistant up to 105°C
- for conductors from 1.5 to 16 mm<sup>2</sup> (AWG 16-6)  
 tin-plated copper  
 dimensional tolerances to DIN 46228 part 4

### General ordering data

Type	H4,0/19,5X GR SV	Version	
Order No.	<a href="#">9006750000</a>	Wire-end ferrule, Standard, 14 mm, 10 mm, grey	
GTIN (EAN)	4008190332297		
Qty.	100 ST		
Type	H6,0/23X GE SV	Version	
Order No.	<a href="#">9006790000</a>	Wire-end ferrule, Standard, 17 mm, 12 mm, yellow	
GTIN (EAN)	4008190332303		
Qty.	100 ST		

### Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	H0,5/12 OR SV	Version
Order No.	<a href="#">9028260000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, orange
GTIN (EAN)	4008190902025	
Qty.	500 ST	
Type	H0,5/14 OR SV	Version
Order No.	<a href="#">9026060000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
GTIN (EAN)	4008190122201	
Qty.	500 ST	
Type	H0,5/14D W SV	Version
Order No.	<a href="#">9019400000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190066024	
Qty.	500 ST	
Type	H0,5/16 OR SV	Version
Order No.	<a href="#">9028270000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, orange
GTIN (EAN)	4008190902049	
Qty.	500 ST	

### packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H0,5/12 OR	Version
Order No.	<a href="#">0409500000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, orange
GTIN (EAN)	4008190090456	
Qty.	500 ST	
Type	H0,5/12D W	Version
Order No.	<a href="#">9019000000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, white
GTIN (EAN)	4008190085728	
Qty.	500 ST	
Type	H0,5/14 OR	Version
Order No.	<a href="#">0690700000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
GTIN (EAN)	4008190015770	
Qty.	500 ST	
Type	H0,5/14D W	Version
Order No.	<a href="#">9019010000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190120931	
Qty.	500 ST	
Type	H0,5/16 OR	Version
Order No.	<a href="#">9025870000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, orange
GTIN (EAN)	4008190025045	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	H0,5/16D W	Version
Order No.	<a href="#">9019020000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, white
GTIN (EAN)	4008190047108	
Qty.	500 ST	
Type	H0,5/18 OR	Version
Order No.	<a href="#">1076980000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, orange
GTIN (EAN)	4032248834631	
Qty.	500 ST	
Type	H0,5/18D W	Version
Order No.	<a href="#">1076990000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, white
GTIN (EAN)	4032248834624	
Qty.	500 ST	

### Strip of wire end ferrules on reel



- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H0,5/14 OR BD GSP	Version
Order No.	<a href="#">9005810000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
GTIN (EAN)	4008190275877	
Qty.	5000 ST	
Type	H0,5/14D W BD GSP	Version
Order No.	<a href="#">9005860000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190275921	
Qty.	5000 ST	

### Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H0,5/14 OR BD	Version
Order No.	<a href="#">9004270000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
GTIN (EAN)	4008190091774	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	H0,5/14D W BD	Version
Order No.	<a href="#">9004280000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190162627	
Qty.	500 ST	
Type	H0,5/14T W BD	Version
Order No.	<a href="#">9021930000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190262402	
Qty.	500 ST	

## Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

## General ordering data

Type	H0,75/12 W SV	Version
Order No.	<a href="#">9028280000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, white
GTIN (EAN)	4008190902216	
Qty.	500 ST	
Type	H0,75/14 W SV	Version
Order No.	<a href="#">9026070000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190187163	
Qty.	500 ST	
Type	H0,75/14D GR SV	Version
Order No.	<a href="#">9019410000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190164096	
Qty.	500 ST	
Type	H0,75/14T HBL SV	Version
Order No.	<a href="#">9021230000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, Light Blue
GTIN (EAN)	4008190153106	
Qty.	500 ST	
Type	H0,75/16 W SV	Version
Order No.	<a href="#">9028290000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, white
GTIN (EAN)	4008190902056	
Qty.	500 ST	
Type	H0,75/18 W SV	Version
Order No.	<a href="#">9028300000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, white
GTIN (EAN)	4008190902063	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H0,75/12 W	Version
Order No.	<a href="#">0409600000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, white
GTIN (EAN)	4008190079826	
Qty.	500 ST	
Type	H0,75/12D GR	Version
Order No.	<a href="#">9019030000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, grey
GTIN (EAN)	4008190127787	
Qty.	500 ST	
Type	H0,75/12T HBL	Version
Order No.	<a href="#">9021030000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, Light Blue
GTIN (EAN)	4008190152901	
Qty.	500 ST	
Type	H0,75/14 W	Version
Order No.	<a href="#">0462900000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190033248	
Qty.	500 ST	
Type	H0,75/14D GR	Version
Order No.	<a href="#">9019040000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190099077	
Qty.	500 ST	
Type	H0,75/16 W	Version
Order No.	<a href="#">9025860000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, white
GTIN (EAN)	4008190141967	
Qty.	500 ST	
Type	H0,75/16D GR	Version
Order No.	<a href="#">9019050000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, grey
GTIN (EAN)	4008190033002	
Qty.	500 ST	
Type	H0,75/16T HBL	Version
Order No.	<a href="#">9021050000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, Light Blue
GTIN (EAN)	4008190096175	
Qty.	500 ST	
Type	H0,75/18 W	Version
Order No.	<a href="#">9025910000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, white
GTIN (EAN)	4008190063702	
Qty.	500 ST	
Type	H0,75/18D GR	Version
Order No.	<a href="#">9019060000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, grey
GTIN (EAN)	4008190049560	
Qty.	500 ST	

## PZ 3 ZERT


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmuller.com

## Accessories

Type	H0,75/18T HBL	Version
Order No.	<a href="#">9021060000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, Light Blue
GTIN (EAN)	4008190071158	
Qty.	500 ST	
Type	H0,75/14T HBL	Version
Order No.	<a href="#">9021040000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, Light Blue
GTIN (EAN)	4008190083168	
Qty.	500 ST	

### Strip of wire end ferrules on reel



- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H0,75/14 W BD GSP	Version
Order No.	<a href="#">9005820000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190275884	
Qty.	5000 ST	
Type	H0,75/14D GR BD GSP	Version
Order No.	<a href="#">9005870000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190275938	
Qty.	5000 ST	
Type	H0,75/14T BL BD GSP	Version
Order No.	<a href="#">9005900000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, Light Blue
GTIN (EAN)	4008190275969	
Qty.	5000 ST	

### Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H0,75/14 W BD	Version
Order No.	<a href="#">9004290000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190006778	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	H0,75/14D GR BD	Version
Order No.	<a href="#">9004300000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190154837	
Qty.	500 ST	
Type	H0,75/14T HBL BD	Version
Order No.	<a href="#">9004310000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, Light Blue
GTIN (EAN)	4008190179298	
Qty.	500 ST	

## Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

## General ordering data

Type	H1,0/12 GE SV	Version
Order No.	<a href="#">9028310000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, yellow
GTIN (EAN)	4008190902070	
Qty.	500 ST	
Type	H1,0/14 GE SV	Version
Order No.	<a href="#">9026080000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow
GTIN (EAN)	4008190026158	
Qty.	500 ST	
Type	H1,0/14D R SV	Version
Order No.	<a href="#">9019420000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190189099	
Qty.	500 ST	
Type	H1,0/16 GE SV	Version
Order No.	<a href="#">9028320000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, yellow
GTIN (EAN)	4008190902087	
Qty.	500 ST	
Type	H1,0/18 GE SV	Version
Order No.	<a href="#">9028340000</a>	Wire-end ferrule, Standard, 15 mm, 12 mm, yellow
GTIN (EAN)	4008190902100	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H1,0/12 GE	Version
Order No.	<a href="#">0409700000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, yellow
GTIN (EAN)	4008190152222	
Qty.	500 ST	
Type	H1,0/12D R	Version
Order No.	<a href="#">9019070000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, red
GTIN (EAN)	4008190029074	
Qty.	500 ST	
Type	H1,0/14 GE	Version
Order No.	<a href="#">0463000000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow
GTIN (EAN)	4008190024697	
Qty.	500 ST	
Type	H1,0/14D R	Version
Order No.	<a href="#">9019080000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190090623	
Qty.	500 ST	
Type	H1,0/16 GE	Version
Order No.	<a href="#">9025950000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, yellow
GTIN (EAN)	4008190037291	
Qty.	500 ST	
Type	H1,0/16D R	Version
Order No.	<a href="#">9019100000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, red
GTIN (EAN)	4008190159986	
Qty.	500 ST	
Type	H1,0/18 GE	Version
Order No.	<a href="#">9025930000</a>	Wire-end ferrule, Standard, 15 mm, 12 mm, yellow
GTIN (EAN)	4008190101497	
Qty.	500 ST	
Type	H1,0/18D R	Version
Order No.	<a href="#">9019110000</a>	Wire-end ferrule, Standard, 15 mm, 12 mm, red
GTIN (EAN)	4008190174828	
Qty.	500 ST	


## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Strip of wire end ferrules on reel



- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

#### General ordering data

Type	H1,0/14 GE BD GSP	Version	
Order No.	<a href="#">9005830000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow	
GTIN (EAN)	4008190275891		
Qty.	5000 ST		

Type	H1,0/14D R BD GSP	Version	
Order No.	<a href="#">9005880000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red	
GTIN (EAN)	4008190275945		
Qty.	5000 ST		

### Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

#### General ordering data

Type	H1,0/14 GE BD	Version	
Order No.	<a href="#">9004320000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow	
GTIN (EAN)	4008190167523		
Qty.	500 ST		

Type	H1,0/14D R BD	Version	
Order No.	<a href="#">9004330000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red	
GTIN (EAN)	4008190047498		
Qty.	500 ST		

Type	H1,0/14T R BD	Version	
Order No.	<a href="#">9021950000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red	
GTIN (EAN)	4008190262747		
Qty.	500 ST		

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H1,5/14 R SV	Version	
Order No.	<a href="#">9026090000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red	
GTIN (EAN)	4008190137168		
Qty.	500 ST		
Type	H1,5/14D SW SV	Version	
Order No.	<a href="#">9019430000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, black	
GTIN (EAN)	4008190107420		
Qty.	500 ST		
Type	H1,5/16 R SV	Version	
Order No.	<a href="#">9028350000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, red	
GTIN (EAN)	4008190902117		
Qty.	500 ST		

### packed loose in polythene bag



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H1,5/14 R	Version	
Order No.	<a href="#">0463100000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red	
GTIN (EAN)	4008190065089		
Qty.	500 ST		
Type	H1,5/14D SW	Version	
Order No.	<a href="#">9019120000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, black	
GTIN (EAN)	4008190153793		
Qty.	500 ST		
Type	H1,5/16 R	Version	
Order No.	<a href="#">0635100000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, red	
GTIN (EAN)	4008190141745		
Qty.	500 ST		

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	H1,5/16D SW	Version
Order No.	<a href="#">9019130000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, black
GTIN (EAN)	4008190023331	
Qty.	500 ST	
Type	H1,5/18D SW	Version
Order No.	<a href="#">9019140000</a>	Wire-end ferrule, Standard, 15 mm, 12 mm, black
GTIN (EAN)	4008190046026	
Qty.	500 ST	
Type	H1,5/24 R	Version
Order No.	<a href="#">0565600000</a>	Wire-end ferrule, Standard, 20 mm, 18 mm, red
GTIN (EAN)	4008190187071	
Qty.	500 ST	
Type	H1,5/24D SW	Version
Order No.	<a href="#">9019150000</a>	Wire-end ferrule, Standard, 20 mm, 18 mm, black
GTIN (EAN)	4008190151676	
Qty.	500 ST	

## Strip of wire end ferrules on reel



- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

## General ordering data

Type	H1,5/14 R BD GSP	Version
Order No.	<a href="#">9005840000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190275907	
Qty.	5000 ST	
Type	H1,5/14D SW BD GSP	Version
Order No.	<a href="#">9005890000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, black
GTIN (EAN)	4008190275952	
Qty.	5000 ST	
Type	H1,5/14S GN BD GSP	Version
Order No.	<a href="#">9028370000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, green
GTIN (EAN)	4032248318537	
Qty.	5000 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code

#### General ordering data

Type	H1,5/14 R BD	Version	
Order No.	<a href="#">9004340000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red	
GTIN (EAN)	4008190080723		
Qty.	500 ST		
Type	H1,5/14D SW BD	Version	
Order No.	<a href="#">9004350000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, black	
GTIN (EAN)	4008190005474		
Qty.	500 ST		
Type	H1,5/14T SW BD	Version	
Order No.	<a href="#">9021960000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, black	
GTIN (EAN)	4008190262389		
Qty.	500 ST		

### Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

#### General ordering data

Type	H2,5/14S BL SV	Version	
Order No.	<a href="#">9046230000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, blue	
GTIN (EAN)	4032248298631		
Qty.	500 ST		
Type	H2,5/15 BL SV	Version	
Order No.	<a href="#">9026100000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, blue	
GTIN (EAN)	4008190141141		
Qty.	500 ST		
Type	H2,5/15T GR SV	Version	
Order No.	<a href="#">9021240000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey	
GTIN (EAN)	4008190115302		
Qty.	500 ST		

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### packed loose in polythene bag



- supplied loose in polybag
- DIN colour code
- other colour code

### General ordering data

Type	H2,5/15D BL	Version
Order No.	<a href="#">9019160000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, blue
GTIN (EAN)	4008190028732	
Qty.	500 ST	
Type	H2,5/15T GR	Version
Order No.	<a href="#">9021070000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190128944	
Qty.	500 ST	
Type	H2,5/19D BL	Version
Order No.	<a href="#">9019170000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, blue
GTIN (EAN)	4008190178024	
Qty.	500 ST	
Type	H2,5/19T GR	Version
Order No.	<a href="#">9021080000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, grey
GTIN (EAN)	4008190149345	
Qty.	500 ST	
Type	H2,5/25D BL	Version
Order No.	<a href="#">9019180000</a>	Wire-end ferrule, Standard, 20 mm, 18 mm, blue
GTIN (EAN)	4008190101145	
Qty.	500 ST	
Type	H2,5/25T GR	Version
Order No.	<a href="#">9021090000</a>	Wire-end ferrule, Standard, 20 mm, 18 mm, grey
GTIN (EAN)	4008190060916	
Qty.	500 ST	

### Strip of wire end ferrules on reel



- Linked wire-end ferrules on reel (5,000 pcs.)
- DIN colour code
- other colour code

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	H2,5/14D BL BD GSP	Version
Order No.	<a href="#">9005850000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, blue
GTIN (EAN)	4008190275914	
Qty.	3000 ST	
Type	H2,5/14T GR BD GSP	Version
Order No.	<a href="#">9005910000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190275976	
Qty.	3000 ST	

### Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- DIN colour code
- other colour code

### General ordering data

Type	H2,5/14D BL BD	Version
Order No.	<a href="#">9004360000</a>	Wire-end ferrule, Standard, 12 mm, 8 mm, blue
GTIN (EAN)	4008190083397	
Qty.	500 ST	
Type	H2,5/14T GR BD	Version
Order No.	<a href="#">9004370000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190052508	
Qty.	500 ST	

### Multi-bag



- In multi-pack bag
- Weidmüller colour code
- Other colour code

### General ordering data

Type	H4,0/18 GR SV	Version
Order No.	<a href="#">9026010000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, grey
GTIN (EAN)	4008190117382	
Qty.	250 ST	
Type	H4,0/18T OR SV	Version
Order No.	<a href="#">9021250000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, orange
GTIN (EAN)	4008190159313	
Qty.	250 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### packed loose in polythene bag



- supplied loose in polybag
- DIN colour code
- other colour code

### General ordering data

Type	H4,0/18D GR	Version
Order No.	<a href="#">9019190000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, grey
GTIN (EAN)	4008190141349	
Qty.	500 ST	
Type	H4,0/18T OR	Version
Order No.	<a href="#">9021100000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, orange
GTIN (EAN)	4008190061708	
Qty.	500 ST	
Type	H4,0/20D GR	Version
Order No.	<a href="#">9019200000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, grey
GTIN (EAN)	4008190126575	
Qty.	500 ST	
Type	H4,0/20T OR	Version
Order No.	<a href="#">9021110000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, orange
GTIN (EAN)	4008190035754	
Qty.	500 ST	
Type	H4,0/26D GR	Version
Order No.	<a href="#">9019210000</a>	Wire-end ferrule, Standard, 20 mm, 18 mm, grey
GTIN (EAN)	4008190002336	
Qty.	100 ST	
Type	H4,0/26T OR	Version
Order No.	<a href="#">9021120000</a>	Wire-end ferrule, Standard, 20 mm, 18 mm, orange
GTIN (EAN)	4008190092825	
Qty.	100 ST	

### Conductor nom. cross-section 6.0mm<sup>2</sup>



6 mm<sup>2</sup>

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

## PZ 3 ZERT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## General ordering data

Type	H6,0/20T GN	Version
Order No.	<a href="#">9021130000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, green
GTIN (EAN)	4008190111731	
Qty.	100 ST	
Type	H6,0/20 SW	Version
Order No.	<a href="#">0533500000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, black
GTIN (EAN)	4008190183905	
Qty.	100 ST	
Type	H6,0/20D GE	Version
Order No.	<a href="#">9019220000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, yellow
GTIN (EAN)	4008190151607	
Qty.	100 ST	
Type	H6,0/26 SW	Version
Order No.	<a href="#">0565700000</a>	Wire-end ferrule, Standard, 20 mm, 18 mm, black
GTIN (EAN)	4008190026837	
Qty.	100 ST	
Type	H6,0/26D GE	Version
Order No.	<a href="#">9019230000</a>	Wire-end ferrule, Standard, 20 mm, 18 mm, yellow
GTIN (EAN)	4008190072117	
Qty.	100 ST	
Type	H6,0/26T GN	Version
Order No.	<a href="#">9021140000</a>	Wire-end ferrule, Standard, 20 mm, 18 mm, green
GTIN (EAN)	4008190022501	
Qty.	100 ST	

## Multi-bag



- Polypropylene conical cable entry funnel
  - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm<sup>2</sup> (AWG 20-7)  
Material: E-Cu, tin galvanised  
Dimensional tolerance acc. to DIN 46228 sect. 4

## General ordering data

Type	H0,75/14S W SV	Version
Order No.	<a href="#">9025700000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190144104	
Qty.	500 ST	
Type	H1,0/14S GE SV	Version
Order No.	<a href="#">9025710000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow
GTIN (EAN)	4008190031442	
Qty.	500 ST	
Type	H1,5/14S R SV	Version
Order No.	<a href="#">9025720000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190072681	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### supplied loose in polybag



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H0,5/16S OR	Version
Order No.	<a href="#">9202900000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, orange
GTIN (EAN)	4032248519026	
Qty.	500 ST	
Type	H4,0/20DS GR	Version
Order No.	<a href="#">9203630000</a>	Wire-end ferrule, Standard, 15 mm, 12 mm, grey
GTIN (EAN)	4032248565078	
Qty.	500 ST	
Type	H0,5/14S OR	Version
Order No.	<a href="#">9004560000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
GTIN (EAN)	4008190286132	
Qty.	500 ST	
Type	H0,5/14S W	Version
Order No.	<a href="#">9004590000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190862060	
Qty.	500 ST	
Type	H0,5/16 DS W	Version
Order No.	<a href="#">9202910000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, white
GTIN (EAN)	4032248519019	
Qty.	500 ST	
Type	H0,75/14DS GR	Version
Order No.	<a href="#">9028580000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4032248159475	
Qty.	500 ST	
Type	H0,75/14S W	Version
Order No.	<a href="#">9025960000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190009878	
Qty.	500 ST	
Type	H0,75/14TS HBL	Version
Order No.	<a href="#">9018550000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, Light Blue
GTIN (EAN)	4008190207991	
Qty.	500 ST	
Type	H0,75/15S W	Version
Order No.	<a href="#">9204240000</a>	Wire-end ferrule, Standard, 10 mm, 9 mm, Light Blue, white
GTIN (EAN)	4032248621545	
Qty.	500 ST	
Type	H1,0/14S GE	Version
Order No.	<a href="#">9025970000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow
GTIN (EAN)	4008190063733	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	H1,0/14S R	Version
Order No.	<a href="#">9018560000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190207984	
Qty.	500 ST	
Type	H1,5/12S R	Version
Order No.	<a href="#">9025690000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, red
GTIN (EAN)	4008190059439	
Qty.	500 ST	
Type	H1,5/14S R	Version
Order No.	<a href="#">9025980000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190080730	
Qty.	500 ST	
Type	H1,5/14DS SW	Version
Order No.	<a href="#">9025240000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, black
GTIN (EAN)	4008190085599	
Qty.	500 ST	
Type	H2,5/12DS BL	Version
Order No.	<a href="#">9028490000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, blue
GTIN (EAN)	4032248049028	
Qty.	500 ST	
Type	H2,5/12TS GR	Version
Order No.	<a href="#">9036200000</a>	Wire-end ferrule, Standard, 8 mm, 6 mm, grey
GTIN (EAN)	4032248067992	
Qty.	500 ST	
Type	H2,5/14DS BL	Version
Order No.	<a href="#">1333100000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, blue
GTIN (EAN)	4008190160364	
Qty.	500 ST	
Type	H2,5/14TS GR	Version
Order No.	<a href="#">9426770000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4032248160693	
Qty.	500 ST	
Type	H2,5/16 TS GR	Version
Order No.	<a href="#">9036210000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, grey
GTIN (EAN)	4032248068005	
Qty.	500 ST	
Type	H2,5/16DS BL	Version
Order No.	<a href="#">9036220000</a>	Wire-end ferrule, Standard, 13 mm, 10 mm, blue
GTIN (EAN)	4032248068012	
Qty.	500 ST	
Type	H4,0/14DS GR	Version
Order No.	<a href="#">9028520000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4032248049035	
Qty.	500 ST	
Type	H4,0/15TS OR	Version
Order No.	<a href="#">9036230000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
GTIN (EAN)	4032248068029	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Nominal conductor cross-section 0.25 mm<sup>2</sup> - 6.0 mm<sup>2</sup>



For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
 tin-plated copper  
 dimensional tolerances to DIN 46228 part 1  
 • supplied loose in polybag

### General ordering data

Type	H0,25/5	Version
Order No.	<a href="#">9018910000</a>	Wire-end ferrule, Standard, 5 mm, 5 mm, No
GTIN (EAN)	4008190068134	
Qty.	1000 ST	
Type	H0,5/10	Version
Order No.	<a href="#">9004050000</a>	Wire-end ferrule, Standard, 10 mm, 10 mm, No
GTIN (EAN)	4008190153052	
Qty.	1000 ST	
Type	H0,5/6	Version
Order No.	<a href="#">0282600000</a>	Wire-end ferrule, Standard, 6 mm, 6 mm, No
GTIN (EAN)	4008190184025	
Qty.	1000 ST	
Type	H0,75/10	Version
Order No.	<a href="#">0542500000</a>	Wire-end ferrule, Standard, 10 mm, 10 mm, No
GTIN (EAN)	4008190037482	
Qty.	1000 ST	
Type	H0,75/6	Version
Order No.	<a href="#">0282700000</a>	Wire-end ferrule, Standard, 6 mm, 6 mm, No
GTIN (EAN)	4008190019013	
Qty.	1000 ST	
Type	H1,0/10	Version
Order No.	<a href="#">0282800000</a>	Wire-end ferrule, Standard, 10 mm, 10 mm, No
GTIN (EAN)	4008190006662	
Qty.	1000 ST	
Type	H1,0/6	Version
Order No.	<a href="#">0372600000</a>	Wire-end ferrule, Standard, 6 mm, 6 mm, No
GTIN (EAN)	4008190180263	
Qty.	1000 ST	
Type	H1,5/10	Version
Order No.	<a href="#">0186500000</a>	Wire-end ferrule, Standard, 10 mm, 10 mm, No
GTIN (EAN)	4008190039592	
Qty.	1000 ST	
Type	H1,5/12	Version
Order No.	<a href="#">9004060000</a>	Wire-end ferrule, Standard, 12 mm, 12 mm, No
GTIN (EAN)	4008190147938	
Qty.	1000 ST	
Type	H1,5/18	Version
Order No.	<a href="#">9004070000</a>	Wire-end ferrule, Standard, 18 mm, 18 mm, No
GTIN (EAN)	4008190105761	
Qty.	1000 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	H1,5/7	Version
Order No.	<a href="#">0372700000</a>	Wire-end ferrule, Standard, 7 mm, 7 mm, No
GTIN (EAN)	4008190064525	
Qty.	1000 ST	
Type	H2,5/10	Version
Order No.	<a href="#">9004080000</a>	Wire-end ferrule, Standard, 10 mm, 10 mm, No
GTIN (EAN)	4008190145446	
Qty.	1000 ST	
Type	H2,5/12	Version
Order No.	<a href="#">0186100000</a>	Wire-end ferrule, Standard, 12 mm, 12 mm, No
GTIN (EAN)	4008190172954	
Qty.	1000 ST	
Type	H2,5/18	Version
Order No.	<a href="#">9004090000</a>	Wire-end ferrule, Standard, 18 mm, 18 mm, No
GTIN (EAN)	4008190147921	
Qty.	1000 ST	
Type	H2,5/7	Version
Order No.	<a href="#">0373000000</a>	Wire-end ferrule, Standard, 7 mm, 7 mm, No
GTIN (EAN)	4008190173463	
Qty.	1000 ST	
Type	H4,0/12	Version
Order No.	<a href="#">0244100000</a>	Wire-end ferrule, Standard, 12 mm, 12 mm, No
GTIN (EAN)	4008190179830	
Qty.	1000 ST	
Type	H4,0/15	Version
Order No.	<a href="#">9004100000</a>	Wire-end ferrule, Standard, 15 mm, 15 mm, No
GTIN (EAN)	4008190119003	
Qty.	500 ST	
Type	H4,0/18	Version
Order No.	<a href="#">9004110000</a>	Wire-end ferrule, Standard, 18 mm, 18 mm, No
GTIN (EAN)	4008190148348	
Qty.	500 ST	
Type	H4,0/9	Version
Order No.	<a href="#">0373100000</a>	Wire-end ferrule, Standard, 9 mm, 9 mm, No
GTIN (EAN)	4008190164669	
Qty.	500 ST	
Type	H6,0/10	Version
Order No.	<a href="#">9004120000</a>	Wire-end ferrule, Standard, 10 mm, 10 mm, No
GTIN (EAN)	4008190104795	
Qty.	500 ST	
Type	H6,0/12	Version
Order No.	<a href="#">0191900000</a>	Wire-end ferrule, Standard, 12 mm, 12 mm, No
GTIN (EAN)	4008190026851	
Qty.	500 ST	
Type	H6,0/15	Version
Order No.	<a href="#">0124700000</a>	Wire-end ferrule, Standard, 15 mm, 15 mm, No
GTIN (EAN)	4008190003807	
Qty.	500 ST	
Type	H6,0/18	Version
Order No.	<a href="#">9004130000</a>	Wire-end ferrule, Standard, 18 mm, 18 mm, No
GTIN (EAN)	4008190143626	
Qty.	500 ST	

**Accessories**

**Assortment of wire end ferrules with plastic collar**



Box filled with wire end ferrules with plastic collar:

- in Weidmüller colour code
- DIN colour code

**General ordering data**

Type	H-BOX 0,14-0,75QMM	Version
Order No.	<a href="#">9025410000</a>	Assortment of wire end ferrules, Box, Colour code: Weidmüller
GTIN (EAN)	4008190341602	
Qty.	1 ST	
Type	H-BOX 0,5-2,5QMM	Version
Order No.	<a href="#">9025900000</a>	Assortment of wire end ferrules, Box, Colour code: Weidmüller
GTIN (EAN)	4008190109202	
Qty.	1 ST	
Type	H-BOX 0,5-2,5QMM DIN	Version
Order No.	<a href="#">9025430000</a>	Assortment of wire end ferrules, Box, Colour code: DIN
GTIN (EAN)	4008190337162	
Qty.	1 ST	
Type	H-BOX 4,0-16,0QMM	Version
Order No.	<a href="#">9025920000</a>	Assortment of wire end ferrules, Box, Colour code: Weidmüller
GTIN (EAN)	4008190101442	
Qty.	1 ST	
Type	H-BOX 4,0-16,0QMM DIN	Version
Order No.	<a href="#">9025400000</a>	Assortment of wire end ferrules, Box, Colour code: DIN
GTIN (EAN)	4008190341596	
Qty.	1 ST	

**Assortment of twin wire end ferrules**



Box filled with twin wire end ferrules with plastic collar:

- in Weidmüller colour code

**General ordering data**

Type	ZH-BOX 0,5-2,5QMM	Version
Order No.	<a href="#">9025390000</a>	Assortment of wire end ferrules, Box, Colour code: Weidmueller
GTIN (EAN)	4008190341015	
Qty.	1 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Multi-bag



- in multipack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H0,5/14 ZH OR SV	Version
Order No.	<a href="#">9004440000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, orange
GTIN (EAN)	4008190198473	
Qty.	500 ST	

Type	H0,5/14D ZH W SV	Version
Order No.	<a href="#">9004780000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, white
GTIN (EAN)	4008190188481	
Qty.	500 ST	

### packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H0,5/14 ZH OR	Version
Order No.	<a href="#">9037200000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, orange
GTIN (EAN)	4008190492397	
Qty.	500 ST	

Type	H0,5/14D ZH W	Version
Order No.	<a href="#">9037380000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, white
GTIN (EAN)	4008190492861	
Qty.	500 ST	

Type	H0,5/16 ZH OR	Version
Order No.	<a href="#">9037210000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, orange
GTIN (EAN)	4008190492687	
Qty.	500 ST	

Type	H0,5/16D ZH W	Version
Order No.	<a href="#">9037390000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, white
GTIN (EAN)	4008190492878	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	H0,5/18 ZH OR	Version
Order No.	<a href="#">9037220000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, orange
GTIN (EAN)	4008190492694	
Qty.	500 ST	
Type	H0,5/18D ZH W	Version
Order No.	<a href="#">9037400000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, white
GTIN (EAN)	4008190492892	
Qty.	500 ST	

## Multi-bag



- in multipack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

## General ordering data

Type	H0,75/14 ZH W SV	Version
Order No.	<a href="#">9018510000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, white
GTIN (EAN)	4008190019914	
Qty.	500 ST	
Type	H0,75/14D ZH GR SV	Version
Order No.	<a href="#">9018520000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, grey
GTIN (EAN)	4008190097998	
Qty.	500 ST	
Type	H0,75/15T ZH BL SV	Version
Order No.	<a href="#">9018570000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, Light Blue
GTIN (EAN)	4008190272630	
Qty.	500 ST	
Type	H0,75/16 ZH W SV	Version
Order No.	<a href="#">9004900000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, white
GTIN (EAN)	4008190482671	
Qty.	500 ST	
Type	H0,75/16D ZH GR SV	Version
Order No.	<a href="#">9004770000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, grey
GTIN (EAN)	4008190038816	
Qty.	500 ST	
Type	H0,75/16T ZH HBL SV	Version
Order No.	<a href="#">9005140000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, Light Blue
GTIN (EAN)	4008190482725	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### packed loose in polythene bag



For the following conductors: 2 No. 0.75 mm<sup>2</sup> (2 No. AWG 18)

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H0,75/14 ZH W	Version
Order No.	<a href="#">9037230000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, white
GTIN (EAN)	4008190853976	
Qty.	500 ST	
Type	H0,75/14D ZH GR	Version
Order No.	<a href="#">9037410000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, grey
GTIN (EAN)	4008190492984	
Qty.	500 ST	
Type	H0,75/14T ZH HBL	Version
Order No.	<a href="#">9037610000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, Light Blue
GTIN (EAN)	4008190493233	
Qty.	500 ST	
Type	H0,75/16 ZH W	Version
Order No.	<a href="#">9037240000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, white
GTIN (EAN)	4008190492717	
Qty.	500 ST	
Type	H0,75/16D ZH GR	Version
Order No.	<a href="#">9037420000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, grey
GTIN (EAN)	4008190492991	
Qty.	500 ST	
Type	H0,75/16T ZH HBL	Version
Order No.	<a href="#">9037620000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, Light Blue
GTIN (EAN)	4008190493264	
Qty.	500 ST	

### supplied loose in polybag



- Polypropylene conical cable entry funnel
  - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm<sup>2</sup> (AWG 20-7)  
 Material: E-Cu, tin galvanised  
 Dimensional tolerance acc. to DIN 46228 sect. 4

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	H0,75/19DS ZH GR	Version	
Order No.	<a href="#">9202830000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, grey	
GTIN (EAN)	4032248515776		
Qty.	500 ST		
Type	H0,75/19S ZH W	Version	
Order No.	<a href="#">9202820000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, white	
GTIN (EAN)	4032248515769		
Qty.	500 ST		
Type	H0,75/19TS ZH HBL	Version	
Order No.	<a href="#">9202840000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, Light Blue	
GTIN (EAN)	4032248515783		
Qty.	500 ST		

### packed loose in polythene bag



For the following conductors: 2 No. 0.75 mm<sup>2</sup> (2 No. AWG 18)

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H0,75/24 ZH W	Version	
Order No.	<a href="#">9037250000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, white	
GTIN (EAN)	4008190492724		
Qty.	500 ST		
Type	H0,75/24D ZH GR	Version	
Order No.	<a href="#">9037430000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, grey	
GTIN (EAN)	4008190493004		
Qty.	500 ST		
Type	H0,75/24T ZH HBL	Version	
Order No.	<a href="#">9037630000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, Light Blue	
GTIN (EAN)	4008190493271		
Qty.	500 ST		

### Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	H1,0/15 ZH GE SV	Version
Order No.	<a href="#">9018530000</a>	Wire-end ferrule, Twin wire-end ferrule, 12 mm, 8 mm, yellow
GTIN (EAN)	4008190066925	
Qty.	500 ST	
Type	H1,0/15D ZH R SV	Version
Order No.	<a href="#">9018540000</a>	Wire-end ferrule, Twin wire-end ferrule, 12 mm, 8 mm, red
GTIN (EAN)	4008190188832	
Qty.	500 ST	
Type	H1,0/15S ZH GE SV	Version
Order No.	<a href="#">9018650000</a>	Wire-end ferrule, Twin wire-end ferrule, 12 mm, 8 mm, yellow
GTIN (EAN)	4032248011407	
Qty.	500 ST	
Type	H1,0/19 ZH GE SV	Version
Order No.	<a href="#">9004910000</a>	Wire-end ferrule, Twin wire-end ferrule, 16 mm, 12 mm, yellow
GTIN (EAN)	4008190482688	
Qty.	500 ST	
Type	H1,0/19D ZH R SV	Version
Order No.	<a href="#">9004760000</a>	Wire-end ferrule, Twin wire-end ferrule, 16 mm, 12 mm, red
GTIN (EAN)	4008190160951	
Qty.	500 ST	

### packed loose in polythene bag



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H1,0/15 ZH GE	Version
Order No.	<a href="#">9037260000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, yellow
GTIN (EAN)	4008190492731	
Qty.	500 ST	
Type	H1,0/15D ZH R	Version
Order No.	<a href="#">9037440000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, red
GTIN (EAN)	4008190493011	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### supplied loose in polybag



- Polypropylene conical cable entry funnel
  - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm<sup>2</sup> (AWG 20-7)  
 Material: E-Cu, tin galvanised  
 Dimensional tolerance acc. to DIN 46228 sect. 4

### General ordering data

Type	H1,0/15S ZH GE	Version	
Order No.	<a href="#">9018690000</a>	Wire-end ferrule, Twin wire-end ferrule, 12 mm, 8 mm, yellow	
GTIN (EAN)	4032248017720		
Qty.	500 ST		

### packed loose in polythene bag



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H1,0/19 ZH GE	Version	
Order No.	<a href="#">9037270000</a>	Wire-end ferrule, Twin wire-end ferrule, 16 mm, 12 mm, yellow	
GTIN (EAN)	4008190492748		
Qty.	500 ST		
Type	H1,0/19D ZH R	Version	
Order No.	<a href="#">9037450000</a>	Wire-end ferrule, Twin wire-end ferrule, 16 mm, 12 mm, red	
GTIN (EAN)	4008190493028		
Qty.	500 ST		

### supplied loose in polybag



- Polypropylene conical cable entry funnel
  - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm<sup>2</sup> (AWG 20-7)  
 Material: E-Cu, tin galvanised  
 Dimensional tolerance acc. to DIN 46228 sect. 4

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	H1,0/22DS R ZH	Version	
Order No.	<a href="#">9036330000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 14 mm, red	
GTIN (EAN)	4032248338566		
Qty.	500 ST		

### packed loose in polythene bag



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H1,0/25 ZH GE	Version	
Order No.	<a href="#">9037280000</a>	Wire-end ferrule, Twin wire-end ferrule, 22 mm, 18 mm, yellow	
GTIN (EAN)	4008190492755		
Qty.	500 ST		

Type	H1,0/25D ZH R	Version	
Order No.	<a href="#">9037460000</a>	Wire-end ferrule, Twin wire-end ferrule, 22 mm, 18 mm, red	
GTIN (EAN)	4008190493035		
Qty.	500 ST		

### Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H1,5/16 ZH R SV	Version	
Order No.	<a href="#">9004410000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, red	
GTIN (EAN)	4008190009397		
Qty.	500 ST		

Type	H1,5/16D ZH SW SV	Version	
Order No.	<a href="#">9004420000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, black	
GTIN (EAN)	4008190167455		
Qty.	500 ST		

Type	H1,5/20 ZH R SV	Version	
Order No.	<a href="#">9004920000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, red	
GTIN (EAN)	4008190482695		
Qty.	500 ST		

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	H1,5/20D SW ZH SV	Version	
Order No.	<a href="#">9004750000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, black	
GTIN (EAN)	4008190055431		
Qty.	500 ST		

### packed loose in polythene bag



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H1,5/16 ZH R	Version	
Order No.	<a href="#">9037290000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, red	
GTIN (EAN)	4008190492762		
Qty.	500 ST		
Type	H1,5/16D ZH SW	Version	
Order No.	<a href="#">9037470000</a>	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, black	
GTIN (EAN)	4008190493042		
Qty.	500 ST		
Type	H1,5/20 ZH R	Version	
Order No.	<a href="#">9037300000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, red	
GTIN (EAN)	4008190492779		
Qty.	500 ST		
Type	H1,5/20D ZH SW	Version	
Order No.	<a href="#">9037480000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, black	
GTIN (EAN)	4008190493059		
Qty.	500 ST		
Type	H1,5/26 ZH R	Version	
Order No.	<a href="#">9037310000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, red	
GTIN (EAN)	4008190492786		
Qty.	100 ST		
Type	H1,5/26D ZH SW	Version	
Order No.	<a href="#">9037490000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, black	
GTIN (EAN)	4008190493066		
Qty.	100 ST		

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- DIN colour code
- other colour code

### General ordering data

Type	H2,5/19D ZH BL SV	Version
Order No.	<a href="#">9004430000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, blue
GTIN (EAN)	4008190099367	
Qty.	250 ST	
Type	H2,5/19T ZH GR SV	Version
Order No.	<a href="#">9018580000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, grey
GTIN (EAN)	4008190272647	
Qty.	250 ST	
Type	H2,5/21 ZH GR SV	Version
Order No.	<a href="#">9005150000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, grey
GTIN (EAN)	4008190482732	
Qty.	250 ST	
Type	H2,5/21D ZH BL SV	Version
Order No.	<a href="#">9004740000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, blue
GTIN (EAN)	4008190031923	
Qty.	250 ST	

### packed loose in polythene bag



- supplied loose in poly-bag
- DIN colour code
- other colour code

### General ordering data

Type	H2,5/19D ZH BL	Version
Order No.	<a href="#">9037500000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, blue
GTIN (EAN)	4008190493073	
Qty.	500 ST	
Type	H2,5/19T ZH GR	Version
Order No.	<a href="#">9037640000</a>	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, grey
GTIN (EAN)	4008190493325	
Qty.	500 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	H2,5/21D ZH BL	Version
Order No.	<a href="#">9037510000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, blue
GTIN (EAN)	4008190493080	
Qty.	100 ST	
Type	H2,5/21T ZH GR	Version
Order No.	<a href="#">9037650000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, grey
GTIN (EAN)	4008190493356	
Qty.	100 ST	
Type	H2,5/27D ZH BL	Version
Order No.	<a href="#">9037520000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, blue
GTIN (EAN)	4008190493097	
Qty.	100 ST	
Type	H2,5/27T ZH GR	Version
Order No.	<a href="#">9037660000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, grey
GTIN (EAN)	4008190493387	
Qty.	100 ST	

## Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- DIN colour code
- other colour code

## General ordering data

Type	H4,0/22T ZH OR SV	Version
Order No.	<a href="#">9018590000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, orange
GTIN (EAN)	4008190272654	
Qty.	100 ST	
Type	H4,0/22D ZH GR SV	Version
Order No.	<a href="#">9004730000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, grey
GTIN (EAN)	4008190161811	
Qty.	100 ST	

## packed loose in polythene bag



- supplied loose in poly-bag
- DIN colour code
- other colour code

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

Type	H4,0/22D ZH GR	Version
Order No.	<a href="#">9037530000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, grey
GTIN (EAN)	4008190493103	
Qty.	100 ST	
Type	H4,0/22T ZH OR	Version
Order No.	<a href="#">9037670000</a>	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, orange
GTIN (EAN)	4008190493431	
Qty.	100 ST	
Type	H4,0/28D ZH GR	Version
Order No.	<a href="#">9037540000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, grey
GTIN (EAN)	4008190493110	
Qty.	100 ST	
Type	H4,0/28T ZH OR	Version
Order No.	<a href="#">9037680000</a>	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, orange
GTIN (EAN)	4008190493479	
Qty.	100 ST	

### Multi-bag



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H6,0/23 ZH SW SV	Version
Order No.	<a href="#">9004930000</a>	Wire-end ferrule, Twin wire-end ferrule, 20 mm, 12 mm, black
GTIN (EAN)	4008190482701	
Qty.	100 ST	
Type	H6,0/23D ZH GE SV	Version
Order No.	<a href="#">9004720000</a>	Wire-end ferrule, Twin wire-end ferrule, 20 mm, 12 mm, yellow
GTIN (EAN)	4008190962210	
Qty.	100 ST	
Type	H6,0/23T ZH GN SV	Version
Order No.	<a href="#">9005160000</a>	Wire-end ferrule, Twin wire-end ferrule, 20 mm, 12 mm, green
GTIN (EAN)	4008190482749	
Qty.	100 ST	

## PZ 3 ZERT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### packed loose in polythene bag



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H6,0/23 ZH SW	Version
Order No.	<a href="#">9037320000</a>	Wire-end ferrule, Twin wire-end ferrule, 20 mm, 12 mm, black
GTIN (EAN)	4008190492793	
Qty.	100 ST	
Type	H6,0/23D ZH GE	Version
Order No.	<a href="#">9037550000</a>	Wire-end ferrule, Twin wire-end ferrule, 20 mm, 12 mm, yellow
GTIN (EAN)	4008190493127	
Qty.	100 ST	
Type	H6,0/23T ZH GN	Version
Order No.	<a href="#">9037690000</a>	Wire-end ferrule, Twin wire-end ferrule, 20 mm, 12 mm, green
GTIN (EAN)	4008190493486	
Qty.	100 ST	
Type	H6,0/29 ZH SW	Version
Order No.	<a href="#">9037330000</a>	Wire-end ferrule, Twin wire-end ferrule, 24 mm, 18 mm, black
GTIN (EAN)	4008190492809	
Qty.	100 ST	
Type	H6,0/29D ZH GE	Version
Order No.	<a href="#">9037560000</a>	Wire-end ferrule, Twin wire-end ferrule, 24 mm, 18 mm, yellow
GTIN (EAN)	4008190493134	
Qty.	100 ST	
Type	H6,0/29T ZH GN	Version
Order No.	<a href="#">9037700000</a>	Wire-end ferrule, Twin wire-end ferrule, 24 mm, 18 mm, green
GTIN (EAN)	4008190493509	
Qty.	100 ST	

### Accessories / replacement parts



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

## PZ 3 ZERT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## General ordering data

Type	ERES PZ 3N	Version
Order No.	<a href="#">1287130000</a>	
GTIN (EAN)	4050118077834	
Qty.	1 ST	

## Replacement parts



After stripping the insulation, a suitable contact or wire end ferrule can be crimped onto the end of the cable. Crimping forms a secure connection between conductor and contact and has largely replaced soldering. Crimping denotes the creation of a homogeneous, permanent connection between conductor and connecting element. The connection can be made only with high-quality precision tools. The result is a secure and reliable connection both in mechanical and electrical terms. Weidmüller offers a wide range of mechanical crimping tools. Integral ratchets with release mechanisms guarantee optimum crimping. Crimped connections made with Weidmüller tools comply with international standards and regulations.

## General ordering data

Type	ERTE GRIFFE PZ	Version
Order No.	<a href="#">9202810000</a>	Pressing tool, Replacement part
GTIN (EAN)	4032248512577	
Qty.	1 ST	