

**STB 14/D5/2.3/M3 SAK2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

**General ordering data**

Version	SAK Series, Socket
Order No.	<a href="#">0168600000</a>
Type	STB 14/D5/2.3/M3 SAK2.5
GTIN (EAN)	4008190135225
Qty.	50 items

**STB 14/D5/2.3/M3 SAK2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	17.5 mm	Depth (inches)	0.689 inch
Diameter	5 mm	Net weight	2.01 g

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

**Material data**

Basic material	Copper - zinc	Surface finish	galvanized
Colour	grey		

**System specifications**

Version For the terminals

**Additional technical data**

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

**Dimensions**

O.D.	5 mm	Diameter	5 mm
Plug-in depth	12.5 mm		

**General**

Installation advice	Direct mounting	Surface finish	galvanized
---------------------	-----------------	----------------	------------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		