

H1,0/10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 10 mm, 10 mm, No |
| Order No. | 0282800000 |
| Type | H1,0/10 |
| GTIN (EAN) | 4008 190006662 |
| Qty. | 1000 items |
| Packaging | loose |

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E499744

Dimensions and weights

Net weight 0.07 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Technical data

| Description of article | Wire end ferrule without plastic collar | Version | Standard |
|------------------------|---|---------|----------|
|------------------------|---|---------|----------|

Wire-end ferrules

| | | | |
|---|-------------------|-----------------------------|----------|
| Contact surface diameter (D1) | 1.4 mm | Contact surface length (L2) | 10 mm |
| Collar diameter (D2) | 2.5 mm | L1 in mm | 10.00 mm |
| Wire connection cross section AWG, max. | AWG 17 | Stripping length | 10 mm |
| Conductor cross-section | 1 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |

Drawings

