

VP 16-MS65

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPMS (blanking plug in brass), Blanking plug, in closed state, PG 16, 6 mm, Brass, nickel-plated
Order No.	0295000000
Type	VP 16-MS65
GTIN (EAN)	4008 19000 1032
Qty.	100 items
Delivery status	This article will no longer be available in the future.
Available until	2024-08-31T00:00:00+02:00
Alternative product	VP 16-K54

VP 16-MS65

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	9 mm	Height (inches)	0.3543 inch
Length	9 mm	Length (inches)	0.3543 inch
Diameter	26 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	5 mm	Net weight	10.55 g

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

General information

Head diameter	26.00 mm	O-Ring	NBR
Silicone	No	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	No
Protection degree	IP68 - 5 bar (30 min.)	Cable gland	PG
Basic material	Brass, nickel-plated	Diameter of sealing ring	22.50 mm
Sealing	NBR	External thread	PG 16
Length of thread	6 mm		

Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

