

## SH 1

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

### General ordering data

Version	Busbar support, beige, 100 °C, Width: 26 mm, V-2, Polyamide 66, when screwed in
Order No.	<a href="#">0299860000</a>
Type	SH 1
GTIN (EAN)	4008190135133
Qty.	20 items

## SH 1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	24 mm	Depth (inches)	0.9449 inch
Height	24.5 mm	Height (inches)	0.9646 inch
Width	26 mm	Width (inches)	1.0236 inch
Net weight	2 g		

### Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Polyamide 66	Surface finish	all others
Colour	beige	UL 94 flammability rating	V-2

### Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
---------------------	-----------------	------------------	-----------------

### Conductors for clamping (rated connection)

Type of connection	Miscellaneous
--------------------	---------------

### General

Number of poles	1	Installation advice	Direct mounting
Operating temperature range, max.	100 °C	Surface finish	all others

### Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		