

AD ST5/E L=1M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

| | |
|------------|--|
| Version | Terminal cover, Transparent, PVC, Height: 62 mm, Width: 1 mm, Depth: 7.1 mm, V-2 |
| Order No. | 0447700000 |
| Type | AD ST5/E L=1M |
| GTIN (EAN) | 4032248147151 |
| Qty. | 1 M |

AD ST5/E L=1M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 7.1 mm | Depth (inches) | 0.2795 inch |
| Height | 62 mm | Height (inches) | 2.4409 inch |
| Width | 1 mm | Width (inches) | 0.0394 inch |
| Net weight | 140 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -50 °C...55 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|-----|--------|-------------|
| Basic material | PVC | Colour | Transparent |
| UL 94 flammability rating | V-2 | | |

System specifications

| | |
|---------|------|
| Version | Hood |
|---------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ETIM 10.0 | EC002848 | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 | | |