


ADP 2/HP2 1M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Similar to illustration *Abbildung ähnlich*

Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

Version	SAK Series, Cover profile, Transparent, 1000 mm
Order No.	0485300000
Type	ADP 2/HP2 1M
GTIN (EAN)	4008190051716
Qty.	20 M

ADP 2/HP2 1M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	61.5 mm	Depth (inches)	2.4213 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	1000 mm	Width (inches)	39.37 inch
Net weight	218 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PVC	Colour	Transparent
UL 94 flammability rating	V-2		

System specifications

Version	cover plate
---------	-------------

Additional technical data

Snap-on	Yes	Installation advice	Direct mounting
---------	-----	---------------------	-----------------


General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

Drawings



Accessories

Protection against contact



Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

Type	HP 2 ADP2	Version	
Order No.	0485660000	End and partition plate for terminals, beige, Height: 59.5 mm, Width:	
GTIN (EAN)	4008190181697	3 mm, V-2, PA 66	
Qty.	20 ST		