

WZAF 120**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The additional connection enables a separate voltage tap. This can be used, for example, for the emergency power supply before the main switch or simply as an additional connection within the application.

General ordering data

Version	Auxiliary connection (terminal)
Order No.	1066300000
Type	WZAF 120
GTIN (EAN)	4008 190024642
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-09-30T00:00:00+02:00

WZAF 120

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	10 mm	Depth (inches)	0.3937 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	8.15 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	tinned copper	Colour	Silver grey
----------------	---------------	--------	-------------

System specifications

Version	Additional connection
---------	-----------------------

Additional technical data

Type of fixing	Snap-on	Installation advice	Feed-through (bushing), Direct mounting
Explosion-tested version	No		

Dimensions

Pitch in mm (P)	27.00 mm
-----------------	----------

General

Installation advice	Feed-through (bushing), Direct mounting
---------------------	--

Rating data

Nominal current	32 A
-----------------	------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-08
ECLASS 15.0	27-25-03-08		