

STB 21.6/IH/VI WTL6/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	Socket (terminal), Plug-in depth: 11.1 mm, 0.00 mm, Depth: 26.6 mm
Order No.	1071030000
Type	STB 21.6/IH/VI WTL6/3
GTIN (EAN)	4008190259235
Qty.	50 items

STB 21.6/IH/VI WTL6/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	26.6 mm	Depth (inches)	1.0472 inch
Height	6.1 mm	Height (inches)	0.2402 inch
Width	6.1 mm	Width (inches)	0.2402 inch
Net weight	2.26 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea		

Material data

Basic material	Polyamide 66	Colour	violet
UL 94 flammability rating	V-2		

System specifications

Version For the terminals

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

Dimensions

Metric size of the thread, external	0.00 mm	Plug-in depth	11.1 mm
-------------------------------------	---------	---------------	---------

General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
---------------------	-----------------	-----------------------------------	--------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		