


WBB ZA WDK2.5/BL5.08**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Partition plate (terminal), orange, Height: 58 mm, Width: 5 mm, V-2, PA 66
Order No.	1072760000
Type	WBB ZA WDK2.5/BL5.08
GTIN (EAN)	4008 1904 70548
Qty.	10 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	45.2 mm	Depth (inches)	1.7795 inch
Height	58 mm	Height (inches)	2.2835 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	7.48 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	936a8f21-8ce1-4838-a60e-9ad69268c052		

Material data

Basic material	PA 66	Colour	orange
UL 94 flammability rating	V-2		

System specifications

Version End and intermediate plate

Additional technical data

Snap-on	No	Installation advice	Direct mounting
---------	----	---------------------	-----------------

General

Installation advice Direct mounting

Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		