

HDC IP68 06B FRAME M6**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**IP68**

The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

General ordering data

Version	HDC enclosures, Installation size: 3, Protection degree: IP66, IP68, in plugged condition, , Clamping yoke connection, Standard, Size of cable entries: none
Order No.	1110890000
Type	HDC IP68 06B FRAME M6
GTIN (EAN)	4032248886951
Qty.	1 items

HDC IP68 06B FRAME M6

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	96 mm	Depth (inches)	3.7795 inch
Height	13 mm	Height (inches)	0.5118 inch
Width	58 mm	Width (inches)	2.2835 inch
Mounting dimension - height	32 mm	Mounting dimension - width	70 mm
Net weight	60 g		

Temperatures

Limit temperature -50 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Chemical resistance	Substance Acetone
	Chemical resistance Resistant
	Substance Diesel oil
	Chemical resistance Unstable
	Substance Ethyl alcohol
	Chemical resistance Resistant
	Substance Transmission oil
	Chemical resistance Conditionally resistant
	Substance Hydraulic oil
	Chemical resistance Conditionally resistant
	Substance Petroleum benzine
	Chemical resistance Unstable
	Substance Sweat
	Chemical resistance Conditionally resistant
	Substance Premium gasoline
	Chemical resistance Unstable
	Substance Water
	Chemical resistance Resistant
	Substance UV
	Chemical resistance Resistant
	Substance Ozone
	Chemical resistance Resistant

Dimensions

Hole pitch length A2	70 mm	Cable entry	No
Total length housing	96 mm	Height of housing B	13 mm

General data

Housing main material	diecast aluminium	Protection degree	IP66, IP68, in plugged condition
EMC housings	Yes		

HDC IP68 06B FRAME M6

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Version**

Number of cable glands	0	Size of cable entries	none
Top part/bottom part/lid	lower part	Cover	without cover
Number of cable entry sideways	0	Design of locking system	Clamping yoke connection
Design	Standard	Installation size	3
Cable entry	No	Type	Bulkhead (feed-through)
Sealing	no sealing	Colour (RAL)	RAL 7001, RAL 9005
BG	3	Suitable for ModuPlug®	Yes

Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC IP68 06B FRAME M6

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings