

**PS\_ZQV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

**General ordering data**

Version	Test adapter (terminal), 1000 V, 20 A
Order No.	<a href="#">1121740000</a>
Type	PS_ZQV
GTIN (EAN)	4032248902675
Qty.	1 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Height	94 mm	Height (inches)	3.7008 inch
Diameter	4 mm	Net weight	14 g

**Temperatures**

Ambient temperature	-5 °C...40 °C
---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	8d191f1d-272c-40a1-8319-7de6fe5d9746

**Material data**

Colour	red
--------	-----

**System specifications**

Version	Test plug
---------	-----------

**Additional technical data**

With snap-in pegs	No	Type of mounting	Plugged
-------------------	----	------------------	---------

**Conductors for clamping (rated connection)**

Stripping length	20 mm	Type of connection	Plug-in connection
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	1.5 mm <sup>2</sup>
Connection cross-section, stranded, max.	1.5 mm <sup>2</sup>		

**Dimensions**

Diameter	4 mm	Pitch in mm (P)	5.40 mm
----------	------	-----------------	---------

**General**

Number of poles	1
-----------------	---

**Rating data**

Rated voltage	1000 V	Max. voltage of clamp support & pluggable system	1000 V
Nominal current	20 A	Current at maximum wires	20 A

**Technical data**

**Classifications**

ETIM 8.0	EC002555	ETIM 9.0	EC002555
ETIM 10.0	EC002555	ECLASS 14.0	27-25-03-04
ECLASS 15.0	27-25-03-04		