

## IE-CD-V04PRJ-C-MA

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Coupling, design for FreeCon PushPull plug-in connectors  
ver.4 according to IEC 61076-3-106, metal

### General ordering data

Version	Junction box, FreeCon, RJ45, Plug-in connector, IP65
Order No.	<a href="#">1122710000</a>
Type	IE-CD-V04PRJ-C-MA
GTIN (EAN)	4032248904778
Qty.	1 items

## IE-CD-V04PRJ-C-MA

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

## Dimensions and weights

Depth	28.2 mm	Depth (inches)	1.1102 inch
Height	52 mm	Height (inches)	2.0472 inch
Width	41 mm	Width (inches)	1.6142 inch
Net weight	243.48 g		

## Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Colour	silver	Housing main material	Aluminium profile, Cover: die-cast zinc, painted
Type of mounting	Screw mounting	Protection degree	IP65
Plugging cycles	750		

## Technical data RJ45 coupling

Current carrying capability (RJ45 coupling)	1 A	Dielectric strength, contact - contact, min. (RJ45 coupling)	≥ 1000 V DC
Housing base material (RJ45 coupling)	Zinc diecast	Category (RJ45 coupling)	Cat.6A / Class EA (ISO/IEC 11801 2010)
Insulation resistance (RJ45 coupling)	> 500 MΩ	Dielectric strength, contact - shielding, max. (RJ45 coupling)	≥ 1500 V DC
Contact resistance (RJ45 coupling)	≤ 20 mΩ		

## Electrical properties

Current-carrying capacity at 50 °C	1 A
------------------------------------	-----

## General standards

Connector standard	IEC 61076-3-106 Var. 4, IEC 60603-7-5	Certificate no. (cULus)	E316369
--------------------	--	-------------------------	---------

## Classifications

ETIM 8.0	EC002597	ETIM 9.0	EC002597
ETIM 10.0	EC002597	ECLASS 14.0	27-44-03-18

---

ECLASS 15.0

27-44-03-18

---

## IE-CD-V04PRJ-C-MA

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Dust caps



For protecting your devices against dust and dirt.

### General ordering data

Type	IE-BP-V04P	Version	
Order No.	<a href="#">1963900000</a>	Flange-mounted housing, protective cap	
GTIN (EAN)	4032248646326		
Qty.	10 ST		

### Sets - RJ45

PushPull plug-in connector set according to IEC 61076-3-106 ver.4 (IEC24702), plastic with RJ45 insert



### General ordering data

Type	IE-PS-V04P-RJ45-FH	Version	
Order No.	<a href="#">1963160000</a>	RJ45 plug, no tools required, Version 4, Cat.6A / Class EA (ISO/IEC 11801 2010)	
GTIN (EAN)	4032248651665		
Qty.	10 ST		