

H0,34/15 ZH TK


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code

General ordering data

| | |
|------------|---|
| Version | Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, Turquoise |
| Order No. | 1139070000 |
| Type | H0,34/15 ZH TK |
| GTIN (EAN) | 403224892047 1 |
| Qty. | 500 items |
| Packaging | loose |

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E354986 |

Dimensions and weights

| | |
|------------|--------|
| Net weight | 0.08 g |
|------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | | | |
|------------------------|----------------------------------|---------|-----------------------|
| Description of article | Twin wire-end ferrule, turquoise | Version | Twin wire-end ferrule |
|------------------------|----------------------------------|---------|-----------------------|

Wire-end ferrules

| | | | |
|---|---------|-----------------------------|----------------------|
| Contact surface diameter (D1) | 1.2 mm | Contact surface length (L2) | 8 mm |
| Collar width (B) | 2 mm | Collar height (A) | 3.5 mm |
| Plastic collar thickness (S2) | 0.25 mm | L1 in mm | 15.00 mm |
| Wire connection cross section AWG, max. | AWG 22 | Metal sleeve thickness (S1) | 0.15 mm |
| Stripping length | 11 mm | Conductor cross-section | 0.34 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |

Drawing

