

CH20M FE 12-67 1.5SN RL


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Functional safety - either fully integrated or simply mounted

The optional "CH20M FE" connection provides optimum protection for your system with a mounting rail contact for functional earthing.

The pre-assembled functional earth contact in a 6 mm housing ensures a reliable connection of electronic shields to the mounting rail. A functional earth contact is available for housings from 12.5 to 67.5 mm, which can be processed using the reflow method.

General ordering data

Version	Electronics housings, Accessories, THT/THR solder connection, 5.00 mm, Number of poles: 1, Solder pin length (l): 1.5 mm, tinned, Silver grey, Tape
Order No.	1189370000
Type	CH20M FE 12-67 1.5SN RL
GTIN (EAN)	4032248972715
Qty.	750 items
Product data	UL:
Packaging	Tape

CH20M FE 12-67 1.5SN RL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	11.7 mm	Depth (inches)	0.4606 inch
Height	13.1 mm	Height (inches)	0.5157 inch
Width	5.4 mm	Width (inches)	0.2126 inch
Net weight	0.48 g		

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Colour	Silver grey	Colour chart (similar)	RAL 7001
Contact surface	tinned	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C		

Rated data acc. to IEC

tested acc. to standard IEC 60664-1, IEC 61984

Material data

Surface finish tinned Basic material Copper alloy

General data

Colour Silver grey Protection degree IP20
 Colour chart (similar) RAL 7001

Important note

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-18-27-92
ECLASS 15.0	27-18-27-92		