


IE-BHS-V14M-RJA-45

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



PushPull plug-in connector according to IEC
61076-3-117 ver.14 (PROFINET), metal, RJ45 empty
housing

General ordering data

Version	Empty enclosure, Flange, angled
Order No.	1296710000
Type	IE-BHS-V14M-RJA-45
GTIN (EAN)	4050118094831
Qty.	10 items

IE-BHS-V14M-RJA-45

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

Dimensions and weights

Depth	54.9 mm	Depth (inches)	2.1614 inch
Height	52.4 mm	Height (inches)	2.063 inch
Width	24.3 mm	Width (inches)	0.9567 inch
Net weight	81.66 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Colour	Miscellaneous	Housing main material	Zinc diecast
Type of mounting	2 screws, M3 (not included)	Protection degree	IP67

General standards

Certificate no. (cULus)	E316369
-------------------------	---------

Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		


IE-BHS-V14M-RJA-45

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Dimensioned drawing



Dimensioned drawing



Installation cut-out

