

**VSPC LOCKING CLIP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The interlock mechanism on the VSPC Series pluggable arrester delivers extra reliability and an improved permanent contact under strong vibrating conditions.

**General ordering data**

Version	Fastening element, Latches
Order No.	<a href="#">1317340000</a>
Type	VSPC LOCKING CLIP
GTIN (EAN)	4050118121179
Qty.	100 items

## VSPC LOCKING CLIP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	13 mm	Height (inches)	0.5118 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	1.34 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Ambient temperature	-40 °C...70 °C
Operating temperature	-40 °C...70 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Optical function display	No	Segment	Measurement - Monitoring - Setting
Version	Latches	Design	miscellaneous
UL 94 flammability rating	V-0	Colour	yellow
Protection degree	IP20		

## Rated data IEC / EN

Signalling contact	No
--------------------	----

## Connection data

Type of connection	Plug / socket
--------------------	---------------

## General data

Protection degree	IP20	Colour	yellow
-------------------	------	--------	--------

## Ratings IECEx/ATEX/cUL

cUL certificate	cUL Certificate - pdf/ VSPC.PDF (application/ pdf)
-----------------	--

## Guarantee

Time interval	5 years
---------------	---------

## Classifications

ETIM 8.0	EC000943	ETIM 9.0	EC000943
ETIM 10.0	EC000943	ECLASS 14.0	27-17-15-01
ECLASS 15.0	27-17-15-01		

**VSPC LOCKING CLIP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

Circuit diagram