

**IE-CD-VAPM24V-C-MA**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Y-distributor / connection coupling, FreeCon for plug-in  
 PushPull Power connector to PROFINET specification,  
 metal

**General ordering data**

Version	Coupling, FreeCon, Supply, IP65, If thread-locking fluid is used
Order No.	<a href="#">1397690000</a>
Type	IE-CD-VAPM24V-C-MA
GTIN (EAN)	4050118198669
Qty.	1 items

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E316369

**Dimensions and weights**

Net weight	425.36 g
------------	----------

**Temperatures**

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Classifications**

ETIM 8.0	EC002597	ETIM 9.0	EC002597
ETIM 10.0	EC002597	ECLASS 14.0	27-44-03-18
ECLASS 15.0	27-44-03-18		


**IE-CD-VAPM24V-C-MA**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

**Drawings**


**Dimensioned drawing**




**Dimensioned drawing**



**Dimensioned drawing**



**Dimensioned drawing**



## IE-CD-VAPM24V-C-MA

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Dust caps



For protecting your devices against dust and dirt.

### General ordering data

Type	IE-BP-VAPP	Version	
Order No.	<a href="#">1068930000</a>	Flange-mounted housing, protective cap	
GTIN (EAN)	4032248823093		
Qty.	10 ST		

### Sets



PushPull Power plug-in connector according to PROFINET specification

### General ordering data

Type	IE-PS-VAPM-5P-2.5	Version	
Order No.	<a href="#">2465440000</a>	Power connector, Plug, PROFINET, Set of connectors	
GTIN (EAN)	4050118522136		
Qty.	1 ST		