

ESO UR20 DIN A4 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Terminal markers, Insert markers, 90 x 8 mm, white
Order No.	1429430000
Type	ESO UR20 DIN A4 WS
GTIN (EAN)	4050118233865
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Available until	2025-08-31T00:00:00+02:00
Alternative product	THM UR20 WS

ESO UR20 DIN A4 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	90 mm	Height (inches)	3.5433 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	11.35 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	9	
Orientation of print	horizontal and vertical	
Number per sheet	60	
Width	8 mm	
UL 94 flammability rating	HB	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Basic material	Paper	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label sheet
Number of markers per combination	1 Label sheet = Insert markers	
Operating temperature range	-40...80 °C	

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

