

PZ 6 ROTO L

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for wire-end ferrules, 0.14mm ² , 6mm ² , Trapezoidal crimp
Order No.	1444050000
Type	PZ 6 ROTO L
GTIN (EAN)	4050118248593
Qty.	1 items

PZ 6 ROTO L

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	80 mm	Height (inches)	3.1496 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	431.4 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	(1)Crimping tool	Version	Mechanical, without interchangeable inserts
------------------------	------------------	---------	---

Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Conductor cross-section, max. AWG	AWG 10
Conductor cross-section, min. AWG	AWG 26	Crimping range, max.	6 mm ²
Crimping range, min.	0.14 mm ²		

tool data crimping

Drive	mechanical	Wire end ferrules cross-section, max.	6 mm ²
Wire end ferrules cross-section, min.	0.14 mm ²	Crimping type/profile	Trapezoidal crimp

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		



Example of use

