

SAI-ADAPT-M8/M12 3P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



M8/M12 and M12/M8 adapters serve for quick implementation of the plug size.

General ordering data

| | |
|------------|----------------------------|
| Version | Y connector, M8 / M12 |
| Order No. | 1473460000 |
| Type | SAI-ADAPT-M8/M12 3P |
| GTIN (EAN) | 4050118279696 |
| Qty. | 1 items |

SAI-ADAPT-M8/M12 3P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

Dimensions and weights

Net weight 12.32 g

Environmental Product Compliance

RoHS Compliance Status Compliant

REACH SVHC Lead 7439-92-1

SCIP 1c533b66-fcff-4da5-b89f-fd55fbf5cb55

Connection data

Single outlet 1 - plug-in connector M8 pin Single outlet 2 - plug-in connector M12 socket

Tightening torque M12: 0.8 Nm, M8: 0.5 Nm

Technical data customisable plug-in connectors

Number of poles 3 Coding M12 = A-coded, M8 = none

Nominal voltage 24 V Protection degree IP67

Pollution severity 3

Standards

Connector standard IEC 61076-2-101, IEC 61076-2-104

General data

Number of poles 3 Coding M12 = A-coded, M8 = none

Connection thread M8 / M12 Nominal voltage 24 V

Protection degree IP67 Pollution severity 3

Connection 1 M8/M12 Connection 2 Screw

Conductor O.D. -

Classifications

ETIM 8.0 EC002925 ETIM 9.0 EC002925

ETIM 10.0 EC002925 ECLASS 14.0 27-44-01-06

ECLASS 15.0 27-44-01-06


SAI-ADAPT-M8/M12 3P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Wiring diagram

