

**IE-FC-SET-SPDED001-KN-P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, Front-Com® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the Front-Com® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

Version	FrontCom, Set
Order No.	<a href="#">1529580000</a>
Type	IE-FC-SET-SPDED001-KN-P
GTIN (EAN)	4050118334432
Qty.	1 items

## IE-FC-SET-SPDED001-KN-P

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	134 mm	Depth (inches)	5.2756 inch
Height	40 mm	Height (inches)	1.5748 inch
Width	67 mm	Width (inches)	2.6378 inch
Net weight	451 g		

### Temperatures

Storage temperature \_\_\_\_\_ Operating temperature \_\_\_\_\_  
 Installation temperature \_\_\_\_\_

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC Potassium perfluorobutane sulfonate 29420-49-3  
 SCIP 8a473a8a-33d4-4318-8088-c28f019e7f77

### General data

Product type	Set		
Protection degree	IP65, in closed state		
Material frame	Zinc diecast		
Material cover	Polycarbonate PC		
Reference product	<a href="#">IE-FC-SFP-KNOB</a> , <a href="#">IE-FC-SP-PWB/2ST</a> , <a href="#">IE-FCI-PWB-DE</a> , <a href="#">IE-BI-USB-A</a> , <a href="#">IE-BI-RJ45-C</a>		
Reference product	Cardinality	1	
	Reference	<a href="#">IE-FC-SFP-KNOB</a>	
	Cardinality	1	
	Reference	<a href="#">IE-FC-SP-PWB/2ST</a>	
	Cardinality	1	
	Reference	<a href="#">IE-FCI-PWB-DE</a>	
	Cardinality	1	
	Reference	<a href="#">IE-BI-USB-A</a>	
Cardinality	1		
Reference	<a href="#">IE-BI-RJ45-C</a>		

### Technical data

Insert plate	2x data, 1x power, Shielded	Frame	Plastic cover
Rated voltage for socket	250 V	Power inserts	Socket DE
Data inserts	USB 2.0 A/A, RJ45 coupling Cat.6A	Rated current for socket	16 A

### General standards

Certificate No. (DNV) TAA000022B

**Technical data**

**Classifications**

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		

**IE-FC-SET-SPDED001-KN-P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

