


**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, orange, 41 A, Number of poles: 3, Pitch in mm (P): 8.00, Insulated: Yes, Width: 22 mm
Order No.	<a href="#">1604300000</a>
Type	WKB 1/3
GTIN (EAN)	4008190010225
Qty.	50 items

## Technical data

### Approvals

RoHS	Conform
------	---------

### Dimensions and weights

Depth	6.1 mm	Depth (inches)	0.2402 inch
Height	9.3 mm	Height (inches)	0.3661 inch
Width	22 mm	Width (inches)	0.8661 inch
Net weight	2.11 g		

### Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Polyamide 66	Colour	orange
UL 94 flammability rating	V-2		

### System specifications

Version	Cross-connector
---------	-----------------

### Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

### Dimensions

Pitch in mm (P)	8.00 mm	TS 35 offset	47 mm
-----------------	---------	--------------	-------

### General

Number of poles	3	Installation advice	Direct mounting
Operating temperature range, max.	100 °C		

### Rating data

Rated voltage	400 V	Nominal current	41 A
---------------	-------	-----------------	------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		