

HDC 64D SDBO 1PG29G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|---|
| Version | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, Side-locking clamp on upper side, high, with cover, Size of cable entries: PG 29 |
| Order No. | 1662280000 |
| Type | HDC 64D SDBO 1PG29G |
| GTIN (EAN) | 4008190418809 |
| Qty. | 1 items |

HDC 64D SDBO 1PG29G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Dimensions and weights

| | | | |
|-----------------------------|---------|----------------------------|-------------|
| Height | 106 mm | Height (inches) | 4.1732 inch |
| Width | 76.8 mm | Width (inches) | 3.0236 inch |
| Mounting dimension - height | 45 mm | Mounting dimension - width | 132 mm |
| Net weight | 558 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | |
|------------------------|--|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP | e98b2b24-ba23-41bf-8d19-0dda3647412f |

| | | |
|---------------------|---------------------|-------------------------|
| Chemical resistance | Substance | Acetone |
| | Chemical resistance | Conditionally resistant |
| | Substance | Drilling oil |
| | Chemical resistance | Resistant |
| | Substance | Diesel |
| | Chemical resistance | Resistant |
| | Substance | Ethyl alcohol |
| | Chemical resistance | Resistant |
| | Substance | Transmission oil |
| | Chemical resistance | Resistant |
| | Substance | Hydraulic oil |
| | Chemical resistance | Resistant |
| | Substance | Coolant |
| | Chemical resistance | Resistant |
| | Substance | Petroleum benzene |
| | Chemical resistance | Resistant |
| | Substance | Sweat |
| | Chemical resistance | Resistant |
| | Substance | Premium gasoline |
| | Chemical resistance | Conditionally resistant |
| Substance | Water | |
| Chemical resistance | Resistant | |
| Substance | UV | |
| Chemical resistance | Unstable | |
| Substance | Ozone | |
| Chemical resistance | Unstable | |

Dimensions

| | | | |
|----------------------|--------|---------------|-----------|
| Hole pitch length A2 | 132 mm | Cable entry | w. thread |
| Width housing C | 43 mm | Width base C1 | 57.5 mm |

HDC 64D SDBO 1PG29G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|----------------------|--------|---------------------|-------|
| Total length housing | 120 mm | Height of housing B | 84 mm |
| Height of base B1 | 5 mm | | |

General data

| | | | |
|----------------|----------------|-------------------|----------------------------|
| Surface finish | Powder coating | Protection degree | IP65, in plugged condition |
|----------------|----------------|-------------------|----------------------------|

Version

| | | | |
|--------------------------------|--------------------|------------------------------|----------------------------------|
| Size of cable entries | PG 29 | Top part/bottom part/lid | lower part |
| Cover | without cover | Number of cable entry on top | 0 |
| Number of cable entry sideways | 1 | Design of cover | with cover |
| Design of housing | Base housing | Design of locking system | Side-locking clamp on upper side |
| Design | high | Installation size | 8 |
| Cable entry | w. thread | Type | Base housing |
| Clamp version | Side-locking clamp | Sealing | NBR |
| Internal thread | PG 29 | Colour (RAL) | RAL 7035 |
| BG | 8 | Suitable for ModuPlug® | Yes |

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ETIM 10.0 | EC000437 | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 | | |

HDC 64D SDBO 1PG29G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC 64D SDBO 1PG29G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC 24B TOBO 1PG29G | Version |
| Order No. | 1662020000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418540 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, Standard, Size of cable entries: PG 29 |
| Type | HDC 64D TOBO 1PG21G | Version |
| Order No. | 1662080000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418601 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, high, Size of cable entries: PG 21 |
| Type | HDC 64D TOBO 1PG29G | Version |
| Order No. | 1662100000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418625 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, high, Size of cable entries: PG 29 |
| Type | HDC 24B TOBO 1M32G | Version |
| Order No. | 1787830000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205271 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, Standard, Size of cable entries: M 32 |

HDC 64D SDBO 1PG29G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 24B TSBO 1PG21G | Version |
| Order No. | 1661860000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418397 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, Standard, Size of cable entries: PG 21 |
| Type | HDC 24B TSBO 1PG29G | Version |
| Order No. | 1661880000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418410 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, Standard, Size of cable entries: PG 29 |
| Type | HDC 64D TSBO 1PG21G | Version |
| Order No. | 1661940000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418472 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, high, Size of cable entries: PG 21 |
| Type | HDC 64D TSBO 1PG29G | Version |
| Order No. | 1661960000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418496 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, high, Size of cable entries: PG 29 |
| Type | HDC 64D TSBO 1M32G | Version |
| Order No. | 1786790000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248204038 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, high, Size of cable entries: M 32 |
| Type | HDC 64D TSBO 1M25G | Version |
| Order No. | 1786800000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248204045 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, high, Size of cable entries: M 25 |
| Type | HDC 24B TSBO 1M32G | Version |
| Order No. | 1787770000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205219 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, Standard, Size of cable entries: M 32 |
| Type | HDC 24B TSBO 1M25G | Version |
| Order No. | 1787780000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205226 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on upper side, Standard, Size of cable entries: M 25 |

HDC 64D SDBO 1PG29G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Cover



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | HDC 24B DODQ 2QB | Version | |
| Order No. | 1009100000 | | |
| GTIN (EAN) | 4032248713844 | | |
| Qty. | 1 ST | | |