

HDC 10A DODL 1LB


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|--|
| Version | HDC enclosures, Installation size: 2, Protection degree: IP65, in plugged condition, Cover for upper part of housing, End-locking clamp, lower side, Standard, Size of cable entries: none |
| Order No. | 1665890000 |
| Type | HDC 10A DODL 1LB |
| GTIN (EAN) | 4008190422929 |
| Qty. | 1 items |

HDC 10A DODL 1LB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 74 mm | Depth (inches) | 2.9134 inch |
| Height | 12.5 mm | Height (inches) | 0.4921 inch |
| Width | 29.5 mm | Width (inches) | 1.1614 inch |
| Length | 63 mm | Length (inches) | 2.4803 inch |
| Net weight | 67 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | |
|------------------------|--|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP | e98b2b24-ba23-41bf-8d19-0dda3647412f |

| | | |
|---------------------|---------------------|-------------------------|
| Chemical resistance | Substance | Acetone |
| | Chemical resistance | Conditionally resistant |
| | Substance | Drilling oil |
| | Chemical resistance | Resistant |
| | Substance | Diesel |
| | Chemical resistance | Resistant |
| | Substance | Ethyl alcohol |
| | Chemical resistance | Resistant |
| | Substance | Transmission oil |
| | Chemical resistance | Resistant |
| | Substance | Hydraulic oil |
| | Chemical resistance | Resistant |
| | Substance | Coolant |
| | Chemical resistance | Resistant |
| | Substance | Petroleum benzine |
| | Chemical resistance | Resistant |
| | Substance | Sweat |
| | Chemical resistance | Resistant |
| | Substance | Premium gasoline |
| | Chemical resistance | Conditionally resistant |
| Substance | Water | |
| Chemical resistance | Resistant | |
| Substance | UV | |
| Chemical resistance | Unstable | |
| Substance | Ozone | |
| Chemical resistance | Unstable | |

HDC 10A DODL 1LB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions

| | | | |
|----------------------|-----------|---------------------|---------|
| Cable entry | For hoods | Width housing C | 29.5 mm |
| Total length housing | 74 mm | Height of housing B | 12.5 mm |

General data

| | | | |
|-------------------|----------------|-----------------------------|-----------------------------|
| Tightening torque | 0.5 Nm | Housing main material | diecast aluminium |
| Surface finish | Powder coating | Protection degree | IP65, in plugged condition |
| EMC housings | No | Material of locking element | Stainless steel, rust-proof |

Version

| | | | |
|--------------------------------|-------------------------------|--------------------------|---------------------------------|
| Size of cable entries | none | Top part/bottom part/lid | Cover |
| Cover | with cover | Tightening torque | 0.5 Nm |
| Number of cable entry sideways | 0 | Design of housing | Cover for upper part of housing |
| Design of locking system | End-locking clamp, lower side | Design | Standard |
| Installation size | 2 | Cable entry | For hoods |
| Type | Cover | Clamp version | End-locking clamp |
| Sealing | no sealing | Colour (RAL) | RAL 7035 |
| BG | 2 | Suitable for ModuPlug® | No |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ETIM 10.0 | EC000437 | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 | | |

HDC 10A DODL 1LB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

