

HDC-C-M20-BCG0.2-0.52AU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	Heavy-duty connectors, Crimp contact, CM 20, Female, Conductor cross-section, max.: 0.52, punched, Copper alloy
Order No.	1682450000
Type	HDC-C-M20-BCG0.2-0.52AU
GTIN (EAN)	4008 19085996 1
Qty.	500 items

HDC-C-M20-BCG0.2-0.52AU

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	0.23 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Contact diameter, male Ø	1 mm	Stripping length, rated connection	2.5 mm
Type of connection	Crimp connection	Version insert	CM 20
Volume resistance	≤5 mΩ	Conductor cross-section, max.	0.52 mm ²
Conductor cross-section, min.	0.2 mm ²	Surface finish	gold
Plugging cycles	≥ 500	Type	Female
Basic material	Copper alloy	Production methods	punched
Cross-section for connected wire	0.2 - 0.52 mm ²	Material of contact	Copper alloy

Classifications


ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

HDC-C-M20-BCG0.2-0.52AU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


Drawings

www.weidmueller.com



Leiterquerschnitt Abisolierlänge

0,08 - 0,20 mm ² AWG 28-24	2,5+0,5 mm
0,20 - 0,52 mm ² AWG 24-20	2,5+0,5 mm




HDC-C-M20-BCG0.2-0.52AU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1.
ChromTop tip, SoftFinish grip

General ordering data

Type	SDS 0.6X3.5X100	Version	
Order No.	9008330000	Screwdriver, Screwdriver	
GTIN (EAN)	4032248056286		
Qty.	1 ST		