

**SKMU PG9-MS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU MS (brass locknut), Locknut, PG 9, 2.8 mm, Brass, nickel-plated
Order No.	<a href="#">1694080000</a>
Type	SKMU PG9-MS
GTIN (EAN)	4008190872243
Qty.	100 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Height	2.8 mm	Height (inches)	0.1102 inch
Net weight	2.2 g		

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

**General information**

O.D.	20.79 mm	Pitch of thread	1.41 mm
Halogen	No	AF size 1	18 mm
Thickness	2.80 mm	Cable gland	PG 9
Basic material	Brass, nickel-plated	External thread	PG 9
Internal thread	PG 9	Length of thread	2.8 mm

**Classifications**

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

**Drawings**

