

TMC 9/20

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The Weidmüller range of conductor and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow conductors right up to cables with large outside diameters. Among the products in the range are combination systems with individual tags, transparent sleeves, shrink-fit sleeves and markers, which can be fixed with cable ties.

General ordering data

Version	TM-I, Socket x 9 mm, PVC, Colour: Transparent, Conductor O.D.: 10 - 317 mm
Order No.	1724790000
Type	TMC 9/20
GTIN (EAN)	4008190373238
Qty.	250 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	20 mm	Height (inches)	0.7874 inch
Width	9 mm	Width (inches)	0.3543 inch
Net weight	0.67 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Number per sheet	50	Type of printing	neutral
Width	9 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Colour	Transparent	Halogen	No
Basic material	PVC	Printed characters	without
Recommended industries	Transportation, Machinery	compatible printer	
Operating temperature range	-40...80 °C		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	150 mm ²
Conductor cross-section, min.	16 mm ²	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor O.D.	10 - 317 mm
Cross-section for connected wire	16 - 150 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		