


**DFFC .5-1.0 ZRV1.5 BAND****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Crimp contact (terminal)
Order No.	<a href="#">1730290000</a>
Type	DFFC .5-1.0 ZRV1.5 BAND
GTIN (EAN)	4008190386733
Qty.	6500 items

**DFFC .5-1.0 ZRV1.5 BAND**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 0.47 g

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Operating temperature	130 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Material data**

Basic material	Wemid	Surface finish	tinned
UL 94 flammability rating	V-0		

**Conductors for clamping (rated connection)**

Stripping length	6 mm	Type of connection	Crimp contact
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	1 mm <sup>2</sup>

**General**

Surface finish tinned

**Classifications**

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		