

**SKMU M32 MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass, nickel-plated
Order No.	<a href="#">1737020000</a>
Type	SKMU M32 MS
GTIN (EAN)	4008 190956493
Qty.	100 items

## SKMU M32 MS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	4 mm	Height (inches)	0.1575 inch
Net weight	2.12 g		

### Temperatures

Operating temperature	
-----------------------	--

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

### General information

O.D.	41.58 mm	Pitch of thread	1.5 mm
Halogen	No	AF size 1	36 mm
Thickness	4.00 mm	Cable gland	M 32
Basic material	Brass, nickel-plated	External thread	M 32
Internal thread	M 32	Length of thread	4 mm

### Classifications

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

