


## LM MT300 40/6 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

### General ordering data

|            |   |
|------------|---|
| Version    | LaserMark, Device markers, 6 x 40 mm, white |
| Order No.  | <a href="#">1760461044</a>                  |
| Type       | LM MT300 40/6 WS                            |
| GTIN (EAN) | 4032248032167                               |
| Qty.       | 10 items                                    |

**LM MT300 40/6 WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.08 mm | Depth (inches)  | 0.0031 inch |
| Height     | 6 mm    | Height (inches) | 0.2362 inch |
| Width      | 40 mm   | Width (inches)  | 1.5748 inch |
| Net weight | 10.03 g |                 |             |

**Temperatures**

Operating temperature range -40...150 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|  |   |             |  |
|--|---|-------------|--|
| Adhesive                                     | Acrylate adhesive                         |             |  |
| Material colour according to resistance code | 9   |             |  |
| Number per sheet                             | 176                                       |             |  |
| Printing method                              | Laser print                               |             |  |
| Version                                      | Self-adhesive                             |             |  |
| Width  | 40 mm                                     |             |  |
| UL 94 flammability rating                    | HB  |             |  |
| Operating temperature range, max.            | 150 °C                                    |             |  |
| Operating temperature range, min.            | -40 °C                                    |             |  |
| Colour                                       | white                                     |             |  |
| Halogen                                      | No  |             |  |
| Basic material                               | Polyester, PVC-free                       |             |  |
| Printed characters                           | without                                   |             |  |
| Number of markers per packaging unit         | 1760                                      |             |  |
| Number of markers per packaging unit         | Form of supply                            | Label sheet |  |
|  | Number of combinations per packaging unit | 10          |  |
|  | Number of markers per combination         | 176         |  |
| Approval acc. to UL 969                      | Yes                                       |             |  |
| Number of markers per combination            | 1 Label sheet = 176 Device markers        |             |  |
| Operating temperature range                  | -40...150 °C                              |             |  |

**Device markers**

Halogen No

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

**Drawings**

