

ADP WF10/WF12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

Version	Bolt-type screw terminals, Cover profile, Transparent, 1000 mm
Order No.	1780940000
Type	ADP WF10/WF12
GTIN (EAN)	4032248241255
Qty.	100 M

ADP WF10/WF12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	6.05 mm	Depth (inches)	0.2382 inch
Height	51.4 mm	Height (inches)	2.0236 inch
Width	1000 mm	Width (inches)	39.37 inch
Net weight	74.25 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material	Polycarbonate	Colour	Transparent
UL 94 flammability rating	V-2		

Additional technical data

Snap-on Yes

Dimensions

Fixing dimension 7 mm

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		