

SAI-4/6/8-MH LEER**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



M12 distributors are available in various versions. The 4, 6 or 8 M12 slots are in 4 or 5 pole design. The group outlet is designed as a fixed cable version, hood version for connection by the user, or with M23. Special versions are also available. For instance, there are 1-to-1 distributors for use with any connection types, or distributors approved for Ex Zone 1.

General ordering data

| | |
|------------|---|
| Version | Hood, 30 V, , LED: No, LED initiator: No, Wiring type: None |
| Order No. | 1783460000 |
| Type | SAI-4/6/8-MH LEER |
| GTIN (EAN) | 4032248183814 |
| Qty. | 1 items |

SAI-4/6/8-MH LEER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 57 mm | Depth (inches) | 2.2441 inch |
| Height | 32.5 mm | Height (inches) | 1.2795 inch |
| Width | 59.2 mm | Width (inches) | 2.3307 inch |
| Net weight | 37.84 g | | |

Temperatures

| | |
|-----------------------|------------|
| Operating temperature | -20 - 90°C |
|-----------------------|------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Connection data

| | | | |
|----------------------|------|----------------------|-------|
| Conductor O.D., min. | 6 mm | Conductor O.D., max. | 12 mm |
| Cable gland | M 20 | Distributor outlet | Hood |

Electrical data

| | | | |
|---|------|--------------------------------|------|
| Rated voltage, min. | 10 V | Rated voltage, max. | 30 V |
| Max. current-carrying capacity per slot | 4 A | Electrical isolation available | No |

General technical data

| | | | |
|-------------------|------|--------------------|----|
| Protection degree | IP68 | Pollution severity | 3 |
| LED | No | LED initiator | No |

Material data

| | | | |
|-------------------------|-------------|--------------------------|----------------|
| Material of distributor | Plastic | Contact material | CuZn |
| Contact surface | Gold-plated | Contact carrier material | PBT (UL 94 V0) |

Technical data cable

| | | | |
|-----------------------------|-------|----------------------|------|
| Conductor O.D., max. | 12 mm | Conductor O.D., min. | 6 mm |
| Suitable for cable carriers | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC003558 | ETIM 9.0 | EC003558 |
| ETIM 10.0 | EC003558 | ECLASS 14.0 | 27-44-01-11 |
| ECLASS 15.0 | 27-44-01-11 | | |

SAI-4/6/8-MH LEER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

M12



Protective caps protect unassigned plug-in stations against external influences.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | SAI-SK-M12 | Version | |
| Order No. | 9456050000 | Protected component assemblies, Protective cap | |
| GTIN (EAN) | 4008190304058 | | |
| Qty. | 30 ST | | |

Screwty® cable gland tool with torque function



The ideal tool for any application
Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | SCREWTY SET -DM | Version | |
| Order No. | 1920000000 | Cable gland tool for M8, M12 lines and connectors | |
| GTIN (EAN) | 4032248436859 | | |
| Qty. | 1 ST | | |

SAI-4/6/8-MH LEER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | ESG 9/20 MC NE WS | Version | |
| Order No. | 1609940000 | | ESG, Device markers x 20 mm, PA 66, Colour: white, pluggable |
| GTIN (EAN) | 4008190203528 | | |
| Qty. | 200 ST | | |