

**HDC 24B SLU 2M25G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

|            |   |
|------------|---|
| Version    | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, Standard, Size of cable entries: M 25 |
| Order No.  | <a href="#">1787880000</a>  |
| Type       | HDC 24B SLU 2M25G   |
| GTIN (EAN) | 4032248205325   |
| Qty.       | 1 items   |

## HDC 24B SLU 2M25G

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

## Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate No. (cURus) | E92202                     |

## Dimensions and weights

|                             |         |                            |             |
|-----------------------------|---------|----------------------------|-------------|
| Height                      | 64 mm   | Height (inches)            | 2.5197 inch |
| Width                       | 76.8 mm | Width (inches)             | 3.0236 inch |
| Mounting dimension - height | 45 mm   | Mounting dimension - width | 132 mm      |
| Net weight                  | 420 g   |                            |             |

## Temperatures

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

## Environmental Product Compliance

|                        |  |                         |
|------------------------|--|-------------------------|
| RoHS Compliance Status | Compliant without exemption                    |                         |
| REACH SVHC             | Potassium perfluorobutane sulfonate 29420-49-3 |                         |
| SCIP                   | e98b2b24-ba23-41bf-8d19-0dda3647412f           |                         |
| Chemical resistance    | Substance                                      | Acetone                 |
|                        | Chemical resistance                            | Conditionally resistant |
|                        | Substance                                      | Drilling oil            |
|                        | Chemical resistance                            | Resistant               |
|                        | Substance                                      | Diesel                  |
|                        | Chemical resistance                            | Resistant               |
|                        | Substance                                      | Ethyl alcohol           |
|                        | Chemical resistance                            | Resistant               |
|                        | Substance                                      | Transmission oil        |
|                        | Chemical resistance                            | Resistant               |
|                        | Substance                                      | Hydraulic oil           |
|                        | Chemical resistance                            | Resistant               |
|                        | Substance                                      | Coolant                 |
|                        | Chemical resistance                            | Resistant               |
|                        | Substance                                      | Petroleum benzine       |
|                        | Chemical resistance                            | Resistant               |
|                        | Substance                                      | Sweat                   |
|                        | Chemical resistance                            | Resistant               |
|                        | Substance                                      | Premium gasoline        |
|                        | Chemical resistance                            | Conditionally resistant |
|                        | Substance                                      | Water                   |
|                        | Chemical resistance                            | Resistant               |
|                        | Substance                                      | UV                      |
|                        | Chemical resistance                            | Unstable                |
|                        | Substance                                      | Ozone                   |
|                        | Chemical resistance                            | Unstable                |

## Dimensions

|                      |        |               |           |
|----------------------|--------|---------------|-----------|
| Hole pitch length A2 | 132 mm | Cable entry   | w. thread |
| Width housing C      | 43 mm  | Width base C1 | 57.5 mm   |

**HDC 24B SLU 2M25G**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

|                      |        |                     |       |
|----------------------|--------|---------------------|-------|
| Total length housing | 120 mm | Height of housing B | 64 mm |
| Height of base B1    | 5 mm   |                     |       |

**General data**

|                             |                             |                |                |
|-----------------------------|-----------------------------|----------------|----------------|
| Housing main material       | diecast aluminium           | Surface finish | Powder coating |
| Protection degree           | IP65, in plugged condition  | EMC housings   | No             |
| Material of locking element | Stainless steel, rust-proof |                |                |

**Version**

|                                |                               |                              |                   |
|--------------------------------|-------------------------------|------------------------------|-------------------|
| Size of cable entries          | M 25                          | Top part/bottom part/lid     | lower part        |
| Cover                          | without cover                 | Number of cable entry on top | 0                 |
| Number of cable entry sideways | 2                             | Design of housing            | Base housing      |
| Design of locking system       | End-locking clamp, lower side | Design                       | Standard          |
| Installation size              | 8                             | Cable entry                  | w. thread         |
| Type                           | Base housing                  | Clamp version                | End-locking clamp |
| Sealing                        | NBR                           | Internal thread              | M 25              |
| Colour (RAL)                   | RAL 7035                      | BG                           | 8                 |
| Suitable for ModuPlug®         | No                            |                              |                   |


**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000437    | ETIM 9.0    | EC000437    |
| ETIM 10.0   | EC000437    | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 |             |             |

**HDC 24B SLU 2M25G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

## HDC 24B SLU 2M25G

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## XXL plug housing, cable entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | HDC 64D TSLU 1M50G         | Version   |
| Order No.  | <a href="#">1111150000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in   |
| GTIN (EAN) | 4032248100118              | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: M 50            |

## Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | HDC 24B TSLU 1PG21G        | Version   |
| Order No.  | <a href="#">1662390000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in   |
| GTIN (EAN) | 4008190418915              | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: PG 21           |
| Type       | HDC 24B TSLU 1PG29G        | Version   |
| Order No.  | <a href="#">1662410000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in   |
| GTIN (EAN) | 4008190418939              | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: PG 29           |

## HDC 24B SLU 2M25G

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | HDC 64D TSLU 1PG21G        | Version   |
| Order No.  | <a href="#">1662470000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in   |
| GTIN (EAN) | 4008190418991              | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, high, Size of cable entries: PG 21               |
| Type       | HDC 64D TSLU 1PG29G        | Version   |
| Order No.  | <a href="#">1662490000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in   |
| GTIN (EAN) | 4008190419011              | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, high, Size of cable entries: PG 29               |
| Type       | HDC 64D TSLU 1M32G         | Version   |
| Order No.  | <a href="#">1786810000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in   |
| GTIN (EAN) | 4032248204052              | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, high, Size of cable entries: M 32                |
| Type       | HDC 24B TSLU 1M32G         | Version   |
| Order No.  | <a href="#">1787790000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in   |
| GTIN (EAN) | 4032248205233              | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: M 32            |
| Type       | HDC 24B TSLU 1M25G         | Version   |
| Order No.  | <a href="#">1787800000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in   |
| GTIN (EAN) | 4032248205240              | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: M 25            |
| Type       | HDC 64D TSLU 1M40G         | Version   |
| Order No.  | <a href="#">1804610000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in   |
| GTIN (EAN) | 4032248267538              | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, high, Size of cable entries: M 40                |

## XXL plug housing, cable entry on top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 64D TOLU 1M50G         | Version  |
| Order No.  | <a href="#">1111170000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4032248100125              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: M 50           |

## HDC 24B SLU 2M25G

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 24B TOLU 1PG21G        | Version  |
| Order No.  | <a href="#">1662540000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4008190419066              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: PG 21          |
| Type       | HDC 24B TOLU 1PG29G        | Version  |
| Order No.  | <a href="#">1662550000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4008190419073              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: PG 29          |
| Type       | HDC 64D TOLU 1PG21G        | Version  |
| Order No.  | <a href="#">1662610000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4008190419134              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, high, Size of cable entries: PG 21              |
| Type       | HDC 64D TOLU 1PG29G        | Version  |
| Order No.  | <a href="#">1662630000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4008190419158              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, high, Size of cable entries: PG 29              |
| Type       | HDC 64D TOLU 1M32G         | Version  |
| Order No.  | <a href="#">1786860000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4032248204106              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, high, Size of cable entries: M 32               |
| Type       | HDC 64D TOLU 1M25G         | Version  |
| Order No.  | <a href="#">1786870000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4032248204113              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, high, Size of cable entries: M 25               |
| Type       | HDC 24B TOLU 1M32G         | Version  |
| Order No.  | <a href="#">1787850000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4032248205295              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: M 32           |
| Type       | HDC 24B TOLU 1M25G         | Version  |
| Order No.  | <a href="#">1787860000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4032248205301              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, Standard, Size of cable entries: M 25           |

**HDC 24B SLU 2M25G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories**

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 64D TOLU 1M40G         | Version  |
| Order No.  | <a href="#">1983470000</a> | HDC enclosures, Installation size: 8, Protection degree: IP65, in  |
| GTIN (EAN) | 4032248687916              | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty.       | 1 ST                       | clamp, lower side, high, Size of cable entries: M 40               |