

**HDC 32A SDBO 2M25G****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

|            |  |
|------------|--|
| Version    | HDC enclosures, Installation size: 7, Protection degree: IP65, in plugged condition, Base housing, Side-locking clamp on upper side, Standard, with cover, Size of cable entries: M 25 |
| Order No.  | <a href="#">1788060000</a>   |
| Type       | HDC 32A SDBO 2M25G   |
| GTIN (EAN) | 4032248205509  |
| Qty.       | 1 items  |

## HDC 32A SDBO 2M25G

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate No. (cURus) | E92202                     |

## Dimensions and weights

|                             |         |                            |             |
|-----------------------------|---------|----------------------------|-------------|
| Height                      | 97 mm   | Height (inches)            | 3.8189 inch |
| Width                       | 89.2 mm | Width (inches)             | 3.5118 inch |
| Mounting dimension - height | 46 mm   | Mounting dimension - width | 92 mm       |
| Net weight                  | 471 g   |                            |             |

## Temperatures

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

## Environmental Product Compliance

|                        |                             |                         |
|------------------------|-----------------------------|-------------------------|
| RoHS Compliance Status | Compliant without exemption |                         |
| REACH SVHC             | No SVHC above 0.1 wt%       |                         |
| Chemical resistance    | Substance                   | Acetone                 |
|                        | Chemical resistance         | Conditionally resistant |
|                        | Substance                   | Drilling oil            |
|                        | Chemical resistance         | Resistant               |
|                        | Substance                   | Diesel                  |
|                        | Chemical resistance         | Resistant               |
|                        | Substance                   | Ethyl alcohol           |
|                        | Chemical resistance         | Resistant               |
|                        | Substance                   | Transmission oil        |
|                        | Chemical resistance         | Resistant               |
|                        | Substance                   | Hydraulic oil           |
|                        | Chemical resistance         | Resistant               |
|                        | Substance                   | Coolant                 |
|                        | Chemical resistance         | Resistant               |
|                        | Substance                   | Petroleum benzine       |
|                        | Chemical resistance         | Resistant               |
|                        | Substance                   | Sweat                   |
|                        | Chemical resistance         | Resistant               |
|                        | Substance                   | Premium gasoline        |
|                        | Chemical resistance         | Conditionally resistant |
|                        | Substance                   | Water                   |
|                        | Chemical resistance         | Resistant               |
|                        | Substance                   | UV                      |
|                        | Chemical resistance         | Unstable                |
|                        | Substance                   | Ozone                   |
|                        | Chemical resistance         | Unstable                |

## Dimensions

|                      |       |               |           |
|----------------------|-------|---------------|-----------|
| Hole pitch length A2 | 92 mm | Cable entry   | w. thread |
| Width housing C      | 56 mm | Width base C1 | 64.5 mm   |

## HDC 32A SDBO 2M25G

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

|                      |       |                     |       |
|----------------------|-------|---------------------|-------|
| Total length housing | 82 mm | Height of housing B | 75 mm |
| Height of base B1    | 5 mm  |                     |       |

## General data

|                             |  |                       |                            |
|-----------------------------|--|-----------------------|----------------------------|
| Tightening torque           | 1.2 Nm   | Housing main material | diecast aluminium          |
| Surface finish              | Powder coating                                   | Protection degree     | IP65, in plugged condition |
| Protection class note       | Protection class for this version of cover: IP20 | EMC housings          | No                         |
| Material of locking element | Stainless steel, rust-proof                      |                       |                            |

## Version

|                              |                                  |                                |                    |
|------------------------------|----------------------------------|--------------------------------|--------------------|
| Size of cable entries        | M 25                             | Top part/bottom part/lid       | lower part         |
| Cover                        | without cover                    | Tightening torque              | 1.2 Nm             |
| Number of cable entry on top | 0                                | Number of cable entry sideways | 2                  |
| Design of cover              | with cover                       | Design of housing              | Base housing       |
| Design of locking system     | Side-locking clamp on upper side | Design                         | Standard           |
| Installation size            | 7                                | Cable entry                    | w. thread          |
| Type                         | Base housing                     | Clamp version                  | Side-locking clamp |
| Sealing                      | NBR                              | Internal thread                | M 25               |
| Colour (RAL)                 | RAL 7035                         | BG                             | 7                  |
| Suitable for ModuPlug®       | No                               |                                |                    |


## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000437    | ETIM 9.0    | EC000437    |
| ETIM 10.0   | EC000437    | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 |             |             |

**HDC 32A SDBO 2M25G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

## HDC 32A SDBO 2M25G

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

| Type       | HDC 32A TOBU 1PG21G        | Version   |
|------------|----------------------------|---|
| Order No.  | <a href="#">1665790000</a> | HDC enclosures, Installation size: 7, Protection degree: IP65, in   |
| GTIN (EAN) | 4008190422813              | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty.       | 1 ST                       | clamp on lower side, Standard, Size of cable entries: PG 21         |
| Type       | HDC 32A TOBU 1PG29G        | Version   |
| Order No.  | <a href="#">1665810000</a> | HDC enclosures, Installation size: 7, Protection degree: IP65, in   |
| GTIN (EAN) | 4008190422837              | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty.       | 1 ST                       | clamp on lower side, Standard, Size of cable entries: PG 29         |
| Type       | HDC 32A TOBU 1M32G         | Version   |
| Order No.  | <a href="#">1787990000</a> | HDC enclosures, Installation size: 7, Protection degree: IP65, in   |
| GTIN (EAN) | 4032248205431              | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty.       | 1 ST                       | clamp on lower side, Standard, Size of cable entries: M 32          |

## Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## HDC 32A SDBO 2M25G

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 32A TSBU 1PG21G        | Version  |
| Order No.  | <a href="#">1665670000</a> | HDC enclosures, Installation size: 7, Protection degree: IP65, in    |
| GTIN (EAN) | 4008190422691              | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty.       | 1 ST                       | clamp on lower side, Standard, Size of cable entries: PG 21          |
| Type       | HDC 32A TSBU 1PG29G        | Version  |
| Order No.  | <a href="#">1665690000</a> | HDC enclosures, Installation size: 7, Protection degree: IP65, in    |
| GTIN (EAN) | 4008190422714              | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty.       | 1 ST                       | clamp on lower side, Standard, Size of cable entries: PG 29          |
| Type       | HDC 32A TSBU 1M32G         | Version  |
| Order No.  | <a href="#">1787950000</a> | HDC enclosures, Installation size: 7, Protection degree: IP65, in    |
| GTIN (EAN) | 4032248205394              | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty.       | 1 ST                       | clamp on lower side, Standard, Size of cable entries: M 32           |
| Type       | HDC 32A TSBU 1M25G         | Version  |
| Order No.  | <a href="#">1787960000</a> | HDC enclosures, Installation size: 7, Protection degree: IP65, in    |
| GTIN (EAN) | 4032248205400              | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty.       | 1 ST                       | clamp on lower side, Standard, Size of cable entries: M 25           |

## Cover



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | HDC 32A DODQ 4BO           | Version   |
| Order No.  | <a href="#">1665920000</a> | HDC enclosures, Installation size: 7, Protection degree: IP65, in |
| GTIN (EAN) | 4008190422950              | plugged condition, Cover for lower part of housing, Side-locking  |
| Qty.       | 1 ST                       | clamp on lower side, Standard, Size of cable entries: none        |