

HDC 06B TSLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|--|
| Version | HDC enclosures, Installation size: 3, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: M 25 |
| Order No. | 1788090000 |
| Type | HDC 06B TSLU 1M25G |
| GTIN (EAN) | 4032248205530 |
| Qty. | 1 items |

HDC 06B TSLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Height | 52 mm | Height (inches) | 2.0472 inch |
| Width | 43 mm | Width (inches) | 1.6929 inch |
| Net weight | 120 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | |
|------------------------|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |
| Chemical resistance | Substance Acetone |
| | Chemical resistance Conditionally resistant |
| | Substance Drilling oil |
| | Chemical resistance Resistant |
| | Substance Diesel |
| | Chemical resistance Resistant |
| | Substance Ethyl alcohol |
| | Chemical resistance Resistant |
| | Substance Transmission oil |
| | Chemical resistance Resistant |
| | Substance Hydraulic oil |
| | Chemical resistance Resistant |
| | Substance Coolant |
| | Chemical resistance Resistant |
| | Substance Petroleum benzine |
| | Chemical resistance Resistant |
| | Substance Sweat |
| | Chemical resistance Resistant |
| | Substance Premium gasoline |
| | Chemical resistance Conditionally resistant |
| | Substance Water |
| | Chemical resistance Resistant |
| | Substance UV |
| | Chemical resistance Unstable |
| | Substance Ozone |
| | Chemical resistance Unstable |

Dimensions

| | | | |
|----------------------|-----------|---------------------|-------|
| Cable entry | w. thread | Width housing C | 43 mm |
| Total length housing | 60 mm | Height of housing B | 52 mm |

HDC 06B TSLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

General data

| | | | |
|-------------------|----------------|-----------------------------|-----------------------------|
| Tightening torque | 1.2 Nm | Housing main material | diecast aluminium |
| Surface finish | Powder coating | Protection degree | IP65, in plugged condition |
| EMC housings | No | Material of locking element | Stainless steel, rust-proof |

Version

| | | | |
|------------------------------|-------------------------------------|--------------------------------|-------------------------------|
| Size of cable entries | M 25 | Top part/bottom part/lid | upper part |
| Cover | without cover | Tightening torque | 1.2 Nm |
| Number of cable entry on top | 0 | Number of cable entry sideways | 1 |
| Design of housing | Cable entry from side, Plug housing | Design of locking system | End-locking clamp, lower side |
| Design | Standard | Installation size | 3 |
| Cable entry | w. thread | Type | Plug |
| Clamp version | End-locking clamp | Sealing | no sealing |
| Internal thread | M 25 | Colour (RAL) | RAL 7035 |
| BG | 3 | Suitable for ModuPlug® | No |


Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ETIM 10.0 | EC000437 | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 | | |

HDC 06B TSLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

HDC 06B TSLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Cover**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC 06B DMCL 1LB | Version |
| Order No. | 1665210000 | HDC enclosures, Installation size: 3, Protection degree: IP65, in |
| GTIN (EAN) | 4008190421915 | plugged condition, Cover for upper part of housing, End-locking |
| Qty. | 1 ST | clamp, lower side, Standard, Size of cable entries: none |