

**CC-H 15/17**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

Version	ClipCard, Accessories, 15 x 17 mm, black
Order No.	<a href="#">1790430000</a>
Type	CC-H 15/17
GTIN (EAN)	4032248215225
Qty.	75 items

## CC-H 15/17

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	5.5 mm	Depth (inches)	0.2165 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	17 mm	Width (inches)	0.6693 inch
Length	17 mm	Length (inches)	0.6693 inch
Diameter	0 mm	Net weight	0.01 g

## Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.009 kg CO2 eq.

## General data

Version	Marker holder	
Width	17 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Colour	black	
Halogen	No	
Length	17 mm	
Basic material	Polyamide 66	
Number of markers per packaging unit	Form of supply	MultiCard
Recommended industries	Machinery	
Number of markers per combination	1 MultiCard = Accessories	
Operating temperature range	-40...100 °C	

## Device markers

Diameter	0 mm	Halogen	No
----------	------	---------	----

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		