



Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

#### General ordering data

Version	TM, Socket x 14 mm, PVC, Colour: Transparent, Conductor O.D.: 10 - 14 mm
Order No.	<a href="#">1806190000</a>
Type	TM 205/12 V0
GTIN (EAN)	4032248275700
Qty.	200 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	14 mm	Depth (inches)	0.5512 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	14 mm	Width (inches)	0.5512 inch
Net weight	0.73 g		

### Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Type of printing	neutral	Width	14 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	Transparent
Basic material	PVC	Recommended industries	Transportation, Machinery
Operating temperature range	-40...80 °C		

### Conductor and cable markers


Conductor cross-section, max.	35 mm <sup>2</sup>	Conductor cross-section, min.	16 mm <sup>2</sup>
Conductor O.D., max.	14 mm	Conductor O.D., min.	10 mm
Conductor O.D.	10 - 14 mm	Cross-section for connected wire	16 - 35 mm <sup>2</sup>

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

## Accessories

## Blank



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	TM-I 12 MC NE BL	Version
Order No.	<a href="#">1718411693</a>	TM-I, Insert markers, 1.5 - 22 mm, 12 x 4 mm, blue
GTIN (EAN)	4008190397456	
Qty.	320 ST	
Type	TM-I 12 MC NE GE	Version
Order No.	<a href="#">1718411687</a>	TM-I, Insert markers, 1.5 - 22 mm, 12 x 4 mm, yellow
GTIN (EAN)	4008190348984	
Qty.	320 ST	
Type	TM-I 12 MC NE GN	Version
Order No.	<a href="#">1718411688</a>	TM-I, Insert markers, 1.5 - 22 mm, 12 x 4 mm, green
GTIN (EAN)	4008190398682	
Qty.	320 ST	
Type	TM-I 12 MC NE RT	Version
Order No.	<a href="#">1718411686</a>	TM-I, Insert markers, 1.5 - 22 mm, 12 x 4 mm, red
GTIN (EAN)	4008190397463	
Qty.	320 ST	
Type	TM-I 12 MC NE WS	Version
Order No.	<a href="#">1718411044</a>	TM-I, Insert markers, 12 x 4 mm, white
GTIN (EAN)	4008190348977	
Qty.	320 ST	
Type	TM-I 12/18 MC NE BL	Version
Order No.	<a href="#">1421160000</a>	TM-I, Insert markers, 1.7 - 79 mm, 30 x 4 mm, blue
GTIN (EAN)	4050118225006	
Qty.	240 ST	
Type	TM-I 12/18 MC NE GE	Version
Order No.	<a href="#">1409630000</a>	TM-I, Insert markers, 1.7 - 79 mm, 30 x 4 mm, yellow
GTIN (EAN)	4050118210835	
Qty.	240 ST	

## Accessories

Type	TM-I 12/18 MC NE GN	Version	
Order No.	<a href="#">1421150000</a>	TM-I, Insert markers, 30 x 4 mm, green	
GTIN (EAN)	4050118224870		
Qty.	240 ST		
Type	TM-I 12/18 MC NE RT	Version	
Order No.	<a href="#">1421170000</a>	TM-I, Insert markers, 1.7 - 79 mm, 30 x 4 mm, red	
GTIN (EAN)	4050118224931		
Qty.	240 ST		
Type	TM-I 12/18 MC NE WS	Version	
Order No.	<a href="#">1323730000</a>	TM-I, Insert markers, 1.7 - 79 mm, 30 x 4 mm, white	
GTIN (EAN)	4050118126785		
Qty.	240 ST		