

SAIS-ZWW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. In special-purpose machine engineering, certain applications require two different lengths of cables which are routed to a single plug-in. To resolve this problem, we offer customisable male plugs and female sockets with two cable outlets. The miniature twin plug comes with a 90° outlet and a straight outlet. The angled version can be rotated as required at 90° intervals.

General ordering data

Version	Field attachable connector, M12
Order No.	1837560000
Type	SAIS-ZWW
GTIN (EAN)	4032248347018
Qty.	1 items

SAIS-ZWW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E307231

Dimensions and weights

Net weight 28.31 g

Environmental Product Compliance

RoHS Compliance Status Compliant

REACH SVHC Lead 7439-92-1

SCIP ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical data customisable plug-in connectors

Number of poles	5	Coding	A-coded
Contact surface	CuSnZn	Type of connection	Screw connection
Housing main material	PA	Conductor cross-section, max.	0.75 mm ²
Conductor cross-section, min.	0.14 mm ²	Nominal voltage	60 V
Nominal current	4 A	Protection degree	IP67
Pollution severity	3	Gender of contact	Male
Shield connection	No	Threaded ring material	Diecast zinc
Temperature range of housing	-25...+85 °C		

General Info

Number of poles	5	Connection 1	M12
Connection 2	Screw	Housing main material	PA
Connection thread	M12	Contact surface	CuSnZn
Protection degree	IP67		

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

Pole scheme



