

**RAHE LN WDT1.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	W-Series, Locking lever
Order No.	<a href="#">1865410000</a>
Type	RAHE LN WDT1.5
GTIN (EAN)	4032248433285
Qty.	10 items

## RAHE LN WDT1.5

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	28 mm	Depth (inches)	1.1024 inch
Height	5 mm	Height (inches)	0.1968 inch
Width	6.4 mm	Width (inches)	0.252 inch
Net weight	0.7 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	PA 66 GF 30	Colour	black
UL 94 flammability rating	HB		

## Additional technical data

Explosion-tested version	No
--------------------------	----

## Dimensions

Pitch in mm (P)	5.00 mm
-----------------	---------

## Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		