

**SCREWTY M12F KO O. SD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The Screwty® attachment is suitable for customisable M12 round plug-in connectors, with an outside dimension of the knurled nut of  $19.8 \pm 0.3$  mm. The tightening torque is 0.8-1.2 Nm.

**General ordering data**

Version	Cable gland tool adapter for M12 connectors
Order No.	<a href="#">1900120000</a>
Type	SCREWTY M12F KO O. SD
GTIN (EAN)	4032248409976
Qty.	1 items
Packaging	Plastic bag

**SCREWTY M12F KO O. SD**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Dimensions and weights**

Net weight	17.8 g
------------	--------

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

**Screwing tools**

Connection thread	M12	Size	19.8 mm
-------------------	-----	------	---------

**Classifications**

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		