

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|--|
| Version | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25 |
| Order No. | 1901150000 |
| Type | HDC 24B SBU 1M25G |
| GTIN (EAN) | 4032248521258 |
| Qty. | 1 items |

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Dimensions and weights

| | | | |
|-----------------------------|--------|----------------------------|-------------|
| Height | 64 mm | Height (inches) | 2.5197 inch |
| Width | 58 mm | Width (inches) | 2.2835 inch |
| Length | 144 mm | Length (inches) | 5.6693 inch |
| Mounting dimension - height | 45 mm | Mounting dimension - width | 132 mm |
| Net weight | 427 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | | |
|------------------------|--|-------------------------|
| RoHS Compliance Status | Compliant without exemption | |
| REACH SVHC | Potassium perfluorobutane sulfonate 29420-49-3 | |
| SCIP | e98b2b24-ba23-41bf-8d19-0dda3647412f | |
| Chemical resistance | Substance | Acetone |
| | Chemical resistance | Conditionally resistant |
| | Substance | Drilling oil |
| | Chemical resistance | Resistant |
| | Substance | Diesel |
| | Chemical resistance | Resistant |
| | Substance | Ethyl alcohol |
| | Chemical resistance | Resistant |
| | Substance | Transmission oil |
| | Chemical resistance | Resistant |
| | Substance | Hydraulic oil |
| | Chemical resistance | Resistant |
| | Substance | Coolant |
| | Chemical resistance | Resistant |
| | Substance | Petroleum benzine |
| | Chemical resistance | Resistant |
| | Substance | Sweat |
| | Chemical resistance | Resistant |
| | Substance | Premium gasoline |
| | Chemical resistance | Conditionally resistant |
| | Substance | Water |
| | Chemical resistance | Resistant |
| | Substance | UV |
| | Chemical resistance | Unstable |
| | Substance | Ozone |
| | Chemical resistance | Unstable |

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions

| | |
|----------------------|--------|
| Hole pitch length A2 | 132 mm |
| Width housing C | 43 mm |
| Total length housing | 144 mm |
| Height of base B1 | 5 mm |

| | |
|---------------------|-----------|
| Cable entry | w. thread |
| Width base C1 | 58 mm |
| Height of housing B | 64 mm |

General data

| | |
|-----------------------------|-----------------------------|
| Housing main material | diecast aluminium |
| Protection degree | IP65, in plugged condition |
| Material of locking element | Stainless steel, rust-proof |

| | |
|----------------|----------------|
| Surface finish | Powder coating |
| EMC housings | No |

Version

| | |
|--------------------------------|----------------------------------|
| Size of cable entries | M 25 |
| Cover | without cover |
| Number of cable entry sideways | 1 |
| Design of locking system | Side-locking clamp on lower side |
| Installation size | 8 |
| Type | Base housing |
| Sealing | NBR |
| Colour (RAL) | RAL 7035 |
| Suitable for ModuPlug® | No |

| | |
|------------------------------|--------------------|
| Top part/bottom part/lid | lower part |
| Number of cable entry on top | 0 |
| Design of housing | Base housing |
| Design | Standard |
| Cable entry | w. thread |
| Clamp version | Side-locking clamp |
| Internal thread | M 25 |
| BG | 8 |

Classifications


| | |
|-------------|-------------|
| ETIM 8.0 | EC000437 |
| ETIM 10.0 | EC000437 |
| ECLASS 15.0 | 27-44-02-02 |

| | |
|-------------|-------------|
| ETIM 9.0 | EC000437 |
| ECLASS 14.0 | 27-44-02-02 |

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC 64D TOBU 2M32G | Version |
| Order No. | 1009710000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248771394 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: M 32 |
| Type | HDC 64D TOBU 1M40G | Version |
| Order No. | 1045560000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248780532 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: M 40 |

XXL plug housing, cable entry on top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC 64D TOBU 1M50G | Version |
| Order No. | 1111140000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248964413 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: M 50 |

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC 24B TOBU 1PG21G | Version |
| Order No. | 1661370000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190417925 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: PG 21 |
| Type | HDC 24B TOBU 1PG29G | Version |
| Order No. | 1661380000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190417932 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: PG 29 |
| Type | HDC 64D TOBU 1PG21G | Version |
| Order No. | 1661440000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190417994 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: PG 21 |
| Type | HDC 64D TOBU 1PG29G | Version |
| Order No. | 1661460000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418014 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: PG 29 |
| Type | HDC 64D TOBU 1M32G | Version |
| Order No. | 1786830000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248204076 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: M 32 |
| Type | HDC 24B TOBU 1M32G | Version |
| Order No. | 1787810000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205257 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: M 32 |
| Type | HDC 24B TOBU 1M25G | Version |
| Order No. | 1787820000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205264 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: M 25 |
| Type | HDC 24B TOBU 1M40G | Version |
| Order No. | 1902980000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248585274 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: M 40 |

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

XXL plug housing, cable entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 64D TSBU 1M50G | Version |
| Order No. | 1111130000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248967711 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: M 50 |

Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 24B TSBU 1PG21G | Version |
| Order No. | 1661230000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190417789 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: PG 21 |
| Type | HDC 24B TSBU 1PG29G | Version |
| Order No. | 1661240000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190417796 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: PG 29 |

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

| Type | HDC 64D TSBU 1PG21G | Version |
|------------|----------------------------|--|
| Order No. | 1661300000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190417857 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: PG 21 |
| Type | HDC 64D TSBU 1PG29G | Version |
| Order No. | 1661320000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190417871 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: PG 29 |
| Type | HDC 64D TSBU 1M32G | Version |
| Order No. | 1786770000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248204014 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: M 32 |
| Type | HDC 64D TSBU 1M25G | Version |
| Order No. | 1786780000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248204021 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: M 25 |
| Type | HDC 24B TSBU 1M32G | Version |
| Order No. | 1787750000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205097 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: M 32 |
| Type | HDC 24B TSBU 1M25G | Version |
| Order No. | 1787760000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205103 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: M 25 |
| Type | HDC 64D TSBU 1M40G | Version |
| Order No. | 1809630000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248284986 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, high, Size of cable entries: M 40 |
| Type | HDC 24B TSBU 1M40G | Version |
| Order No. | 1902480000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248592944 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: M 40 |

Cover



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**General ordering data**

| | | |
|------------|----------------------------|---|
| Type | HDC 24B DODQ 4BO | Version |
| Order No. | 1665630000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190422653 | plugged condition, Cover for lower part of housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: none |

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Counterpart

Bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC 24B ABU | Version |
| Order No. | 1212400000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190083939 | plugged condition, Bulkhead housing, Side-locking clamp on lower |
| Qty. | 1 ST | side, Side-locking clamp not replaceable, Standard, Size of cable entries: none |
| Type | HDC 24B ABU N | Version |
| Order No. | 2488600000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4050118541533 | plugged condition, Bulkhead housing, Side-locking clamp on lower |
| Qty. | 1 ST | side, Standard, Size of cable entries: none |

Coupling hood



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC 24B KBU 1M25G | Version |
| Order No. | 1787920000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205363 | plugged condition, Coupling housing, Side-locking clamp on lower |
| Qty. | 1 ST | side, Standard, Size of cable entries: M 25 |

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Counterpart

| | | |
|------------|----------------------------|---|
| Type | HDC 24B KBU 1PG21G | Version |
| Order No. | 1661720000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418274 | plugged condition, Coupling housing, Side-locking clamp on lower |
| Qty. | 1 ST | side, Standard, Size of cable entries: PG 21 |
| Type | HDC 24B KBU 1PG29G | Version |
| Order No. | 1661730000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418281 | plugged condition, Coupling housing, Side-locking clamp on lower |
| Qty. | 1 ST | side, Standard, Size of cable entries: PG 29 |
| Type | HDC 64D KBU 1M32G | Version |
| Order No. | 1786960000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248204205 | plugged condition, Coupling housing, Side-locking clamp on lower |
| Qty. | 1 ST | side, high, Size of cable entries: M 32 |
| Type | HDC 64D KBU 1PG29G | Version |
| Order No. | 1661810000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418359 | plugged condition, Coupling housing, Side-locking clamp on lower |
| Qty. | 1 ST | side, high, Size of cable entries: PG 29 |

Base housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 24B SBU 1M25G | Version |
| Order No. | 1901150000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248521258 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | Standard, Size of cable entries: M 25 |
| Type | HDC 24B SBU 1M25G N | Version |
| Order No. | 2560960000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4050118673227 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | Standard, Size of cable entries: M 25 |
| Type | HDC 24B SBU 1PG21G | Version |
| Order No. | 1661510000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418069 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | Standard, Size of cable entries: PG 21 |
| Type | HDC 24B SBU 1PG21G N | Version |
| Order No. | 2560750000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4050118676747 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | Standard, Size of cable entries: M 25 |

HDC 24B SBU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Counterpart

| | | |
|------------|----------------------------|--|
| Type | HDC 24B SBU 2M25G | Version |
| Order No. | 1787870000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205318 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | Standard, Size of cable entries: M 25 |
| Type | HDC 24B SBU 2PG21G | Version |
| Order No. | 1661520000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418076 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | Standard, Size of cable entries: PG 21 |
| Type | HDC 24B SBU 2M25G N | Version |
| Order No. | 2560970000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4050118676730 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | Standard, Size of cable entries: M 25 |
| Type | HDC 64D SBU 1M25G | Version |
| Order No. | 1904340000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248585601 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: M 25 |
| Type | HDC 64D SBU 1M32G | Version |
| Order No. | 1904350000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248585298 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: M 32 |
| Type | HDC 64D SBU 1M32G N | Version |
| Order No. | 2561050000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4050118680195 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: M 32 |
| Type | HDC 64D SBU 2M25G | Version |
| Order No. | 1786890000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248204137 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: M 25 |
| Type | HDC 64D SBU 2M25G N | Version |
| Order No. | 2561060000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4050118680508 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: M 32 |
| Type | HDC 64D SBU 2M32G | Version |
| Order No. | 1786880000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248204120 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: M 32 |
| Type | HDC 64D SBU 2M32G N | Version |
| Order No. | 2550540000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4064675005087 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: M 32 |
| Type | HDC 64D SBU 2PG21G | Version |
| Order No. | 1661590000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418144 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: PG 21 |
| Type | HDC 64D SBU 2PG29G | Version |
| Order No. | 1661630000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418182 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: PG 29 |
| Type | HDC 64D SBU 2PG29G N | Version |
| Order No. | 2560790000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4050118894103 | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty. | 1 ST | high, Size of cable entries: M 32 |