

HDC 24B SDLU 1M25G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|---|
| Version | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: M 25 |
| Order No. | 1901480000 |
| Type | HDC 24B SDLU 1M25G |
| GTIN (EAN) | 4032248521364 |
| Qty. | 1 items |

HDC 24B SDLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Dimensions and weights

| | | | |
|-----------------------------|---------|----------------------------|-------------|
| Height | 86 mm | Height (inches) | 3.3858 inch |
| Width | 98.8 mm | Width (inches) | 3.8898 inch |
| Mounting dimension - height | 45 mm | Mounting dimension - width | 132 mm |
| Net weight | 540 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | |
|------------------------|--|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP | e98b2b24-ba23-41bf-8d19-0dda3647412f |

| | | |
|---------------------|---------------------|-------------------------|
| Chemical resistance | Substance | Acetone |
| | Chemical resistance | Conditionally resistant |
| | Substance | Drilling oil |
| | Chemical resistance | Resistant |
| | Substance | Diesel |
| | Chemical resistance | Resistant |
| | Substance | Ethyl alcohol |
| | Chemical resistance | Resistant |
| | Substance | Transmission oil |
| | Chemical resistance | Resistant |
| | Substance | Hydraulic oil |
| | Chemical resistance | Resistant |
| | Substance | Coolant |
| | Chemical resistance | Resistant |
| | Substance | Petroleum benzene |
| | Chemical resistance | Resistant |
| | Substance | Sweat |
| | Chemical resistance | Resistant |
| | Substance | Premium gasoline |
| | Chemical resistance | Conditionally resistant |
| Substance | Water | |
| Chemical resistance | Resistant | |
| Substance | UV | |
| Chemical resistance | Unstable | |
| Substance | Ozone | |
| Chemical resistance | Unstable | |

Dimensions

| | | | |
|----------------------|--------|---------------|-----------|
| Hole pitch length A2 | 132 mm | Cable entry | w. thread |
| Width housing C | 43 mm | Width base C1 | 57.5 mm |

HDC 24B SDLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|----------------------|--------|---------------------|-------|
| Total length housing | 120 mm | Height of housing B | 64 mm |
| Height of base B1 | 5 mm | | |

General data

| | | | |
|----------------|----------------|-------------------|----------------------------|
| Surface finish | Powder coating | Protection degree | IP65, in plugged condition |
|----------------|----------------|-------------------|----------------------------|

Version

| | | | |
|--------------------------------|-------------------|------------------------------|-------------------------------|
| Size of cable entries | M 25 | Top part/bottom part/lid | lower part |
| Cover | with cover | Number of cable entry on top | 0 |
| Number of cable entry sideways | 1 | Design of cover | with cover |
| Design of housing | Base housing | Design of locking system | End-locking clamp, lower side |
| Design | Standard | Installation size | 8 |
| Cable entry | w. thread | Type | Base housing |
| Clamp version | End-locking clamp | Sealing | NBR |
| Internal thread | M 25 | Colour (RAL) | RAL 7035 |
| BG | 8 | Suitable for ModuPlug® | No |

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ETIM 10.0 | EC000437 | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 | | |

HDC 24B SDLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC 24B SDLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

XXL plug housing, cable entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | | |
|------------|----------------------------|---------|---|
| Type | HDC 64D TSLU 1M50G | Version | |
| Order No. | 1111150000 | | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248100118 | | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty. | 1 ST | | clamp, lower side, Standard, Size of cable entries: M 50 |

Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | | |
|------------|----------------------------|---------|---|
| Type | HDC 24B TSLU 1PG21G | Version | |
| Order No. | 1662390000 | | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418915 | | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty. | 1 ST | | clamp, lower side, Standard, Size of cable entries: PG 21 |
| Type | HDC 24B TSLU 1PG29G | Version | |
| Order No. | 1662410000 | | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418939 | | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty. | 1 ST | | clamp, lower side, Standard, Size of cable entries: PG 29 |

HDC 24B SDLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | HDC 64D TSLU 1PG21G | Version |
| Order No. | 1662470000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190418991 | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty. | 1 ST | clamp, lower side, high, Size of cable entries: PG 21 |
| Type | HDC 64D TSLU 1PG29G | Version |
| Order No. | 1662490000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4008190419011 | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty. | 1 ST | clamp, lower side, high, Size of cable entries: PG 29 |
| Type | HDC 64D TSLU 1M32G | Version |
| Order No. | 1786810000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248204052 | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty. | 1 ST | clamp, lower side, high, Size of cable entries: M 32 |
| Type | HDC 24B TSLU 1M32G | Version |
| Order No. | 1787790000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205233 | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty. | 1 ST | clamp, lower side, Standard, Size of cable entries: M 32 |
| Type | HDC 24B TSLU 1M25G | Version |
| Order No. | 1787800000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205240 | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty. | 1 ST | clamp, lower side, Standard, Size of cable entries: M 25 |
| Type | HDC 64D TSLU 1M40G | Version |
| Order No. | 1804610000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248267538 | plugged condition, Cable entry from side, Plug housing, End-locking |
| Qty. | 1 ST | clamp, lower side, high, Size of cable entries: M 40 |

XXL plug housing, cable entry on top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 64D TOLU 1M50G | Version |
| Order No. | 1111170000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248100125 | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty. | 1 ST | clamp, lower side, Standard, Size of cable entries: M 50 |

HDC 24B SDLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 24B TOLU 1PG21G | Version |
| Order No. | 1662540000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 21 |
| GTIN (EAN) | 4008190419066 | |
| Qty. | 1 ST | |
| Type | HDC 24B TOLU 1PG29G | Version |
| Order No. | 1662550000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 29 |
| GTIN (EAN) | 4008190419073 | |
| Qty. | 1 ST | |
| Type | HDC 64D TOLU 1PG21G | Version |
| Order No. | 1662610000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: PG 21 |
| GTIN (EAN) | 4008190419134 | |
| Qty. | 1 ST | |
| Type | HDC 64D TOLU 1PG29G | Version |
| Order No. | 1662630000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: PG 29 |
| GTIN (EAN) | 4008190419158 | |
| Qty. | 1 ST | |
| Type | HDC 64D TOLU 1M32G | Version |
| Order No. | 1786860000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: M 32 |
| GTIN (EAN) | 4032248204106 | |
| Qty. | 1 ST | |
| Type | HDC 64D TOLU 1M25G | Version |
| Order No. | 1786870000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: M 25 |
| GTIN (EAN) | 4032248204113 | |
| Qty. | 1 ST | |
| Type | HDC 24B TOLU 1M32G | Version |
| Order No. | 1787850000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: M 32 |
| GTIN (EAN) | 4032248205295 | |
| Qty. | 1 ST | |
| Type | HDC 24B TOLU 1M25G | Version |
| Order No. | 1787860000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: M 25 |
| GTIN (EAN) | 4032248205301 | |
| Qty. | 1 ST | |

HDC 24B SDLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | HDC 64D TOLU 1M40G | Version |
| Order No. | 1983470000 | HDC enclosures, Installation size: 8, Protection degree: IP65, in |
| GTIN (EAN) | 4032248687916 | plugged condition, Cable entry from top, Plug housing, End-locking |
| Qty. | 1 ST | clamp, lower side, high, Size of cable entries: M 40 |