

HDC 32B KBU 1M40G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|---|
| Version | HDC enclosures, Installation size: 10, Protection degree: IP65, in plugged condition, Coupling housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 40 |
| Order No. | 1902730000 |
| Type | HDC 32B KBU 1M40G |
| GTIN (EAN) | 4032248585670 |
| Qty. | 1 items |

HDC 32B KBU 1M40G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 139.4 mm | Depth (inches) | 5.4882 inch |
| Height | 83 mm | Height (inches) | 3.2677 inch |
| Width | 97 mm | Width (inches) | 3.8189 inch |
| Net weight | 419.76 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | |
|------------------------|--|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP | e98b2b24-ba23-41bf-8d19-0dda3647412f |

| | | |
|---------------------|---------------------|-------------------------|
| Chemical resistance | Substance | Acetone |
| | Chemical resistance | Conditionally resistant |
| | Substance | Drilling oil |
| | Chemical resistance | Resistant |
| | Substance | Diesel |
| | Chemical resistance | Resistant |
| | Substance | Ethyl alcohol |
| | Chemical resistance | Resistant |
| | Substance | Transmission oil |
| | Chemical resistance | Resistant |
| | Substance | Hydraulic oil |
| | Chemical resistance | Resistant |
| | Substance | Coolant |
| | Chemical resistance | Resistant |
| | Substance | Petroleum benzine |
| | Chemical resistance | Resistant |
| | Substance | Sweat |
| | Chemical resistance | Resistant |
| | Substance | Premium gasoline |
| | Chemical resistance | Conditionally resistant |
| | Substance | Water |
| | Chemical resistance | Resistant |
| | Substance | UV |
| | Chemical resistance | Unstable |
| | Substance | Ozone |
| | Chemical resistance | Unstable |

Dimensions

| | | | |
|----------------------|-----------|---------------------|---------|
| Cable entry | w. thread | Width housing C | 82.5 mm |
| Total length housing | 94 mm | Height of housing B | 83 mm |

HDC 32B KBU 1M40G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

General data

| | | | |
|-------------------|----------------|-----------------------------|-----------------------------|
| Tightening torque | 2 Nm | Housing main material | diecast aluminium |
| Surface finish | Powder coating | Protection degree | IP65, in plugged condition |
| EMC housings | No | Material of locking element | Stainless steel, rust-proof |

Version

| | | | |
|------------------------------|--------------------|--------------------------------|----------------------------------|
| Size of cable entries | M 40 | Top part/bottom part/lid | lower part |
| Cover | without cover | Tightening torque | 2 Nm |
| Number of cable entry on top | 1 | Number of cable entry sideways | 0 |
| Design of housing | Coupling housing | Design of locking system | Side-locking clamp on lower side |
| Design | Standard | Installation size | 10 |
| Cable entry | w. thread | Type | coupling extension |
| Clamp version | Side-locking clamp | Sealing | NBR |
| Internal thread | M 40 | Colour (RAL) | RAL 7035 |
| BG | 10 | Suitable for ModuPlug® | Yes |


Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ETIM 10.0 | EC000437 | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 | | |

HDC 32B KBU 1M40G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

HDC 32B KBU 1M40G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Housing, cable entry sideways**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.
The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.
The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.
The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.
Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 32B TSBU 1PG29G | Version |
| Order No. | 1666840000 | HDC enclosures, Installation size: 10, Protection degree: IP65, in |
| GTIN (EAN) | 4008190424046 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: PG 29 |
| Type | HDC 32B TSBU 1M32G | Version |
| Order No. | 1788400000 | HDC enclosures, Installation size: 10, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205936 | plugged condition, Cable entry from side, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: M 32 |

Housing, cable entry at top

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.
The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.
The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.
The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.
Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC 32B TOBU 1M40G | Version |
| Order No. | 1221070000 | HDC enclosures, Installation size: 10, Protection degree: IP65, in |
| GTIN (EAN) | 4032248998180 | plugged condition, Plug housing, Cable entry from top, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: M 40 |

HDC 32B KBU 1M40G

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | HDC 32B TOBU 1PG29G | Version |
| Order No. | 1666870000 | HDC enclosures, Installation size: 10, Protection degree: IP65, in |
| GTIN (EAN) | 4008190424077 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: PG 29 |
| Type | HDC 32B TOBU 1M32G | Version |
| Order No. | 1788430000 | HDC enclosures, Installation size: 10, Protection degree: IP65, in |
| GTIN (EAN) | 4032248205967 | plugged condition, Cable entry from top, Plug housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: M 32 |

Cover

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 32B DODQ 4BO | Version |
| Order No. | 1165790000 | HDC enclosures, Installation size: 10, Protection degree: IP65, in |
| GTIN (EAN) | 4032248964512 | plugged condition, Cover for lower part of housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard |