

**GWDR M12-NP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|            |  |
|------------|--|
| Version    | GWDR NP (flat gasket - neoprene), Sealing ring, M 12, Neoprene |
| Order No.  | <a href="#">1913320000</a>                                     |
| Type       | GWDR M12-NP  |
| GTIN (EAN) | 4032248543663  |
| Qty.       | 50 items   |

**GWDR M12-NP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 1.2 mm | Height (inches) | 0.0472 inch |
| Net weight | 0.32 g |                 |             |

**Temperatures**

Operating temperature -40 °C... 100 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

|                                   |          |                                   |            |
|-----------------------------------|----------|-----------------------------------|------------|
| Silicone                          | No       | Number of wires                   | 1          |
| O.D.                              | 18 mm    | Operating temperature range, max. | 100 °C     |
| Operating temperature range, min. | -40 °C   | Pitch of thread                   | 1.5 mm     |
| Halogen                           | Yes      | Thickness                         | 1.20 mm    |
| Cable gland                       | M 12     | Basic material                    | Neoprene   |
| Diameter of sealing ring          | 18.00 mm | Sealing                           | Neoprene   |
| External thread                   | M 12     | Internal thread                   | M 12 x 1.5 |
| Inside diameter D2                | 12.00 mm |                                   |            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001181    | ETIM 9.0    | EC001181    |
| ETIM 10.0   | EC001181    | ECLASS 14.0 | 27-43-03-19 |
| ECLASS 15.0 | 27-43-03-19 |             |             |

**Drawings**

